



CERTIFICATE

FOR EUROPEAN PRODUCT SAFETY

Reference No. SE-S-2100505

Installation coupler for fixed installation

Type designation: 2379237-*, 1-2379237-*, 2379238-*, 1-2379238-*, 2379239-*,
1-2379239-*, 2379240-*, 1-2379240-*, 2359422-*, 1-2359422-*,
2359518-*, 1-2359518-*, 2359420-*, 2359421-*

Certificate holder: Tyco Electronics Austria GmbH
Schrackstrasse 1,
3830 Waidhofen / Thaya
Austria

The product complies with the standard(s): EN IEC 61535:2019

Date of expiry: 13 April, 2026

EU Directive information: According to the principle of presumption of conformity, this certificate constitutes support for an EC Declaration of Conformity and CE marking according to the Low Voltage Directive 2014/35/EU.

Additional information in Appendix

Certification Body: Intertek Semko AB, Product Certification **Place:** Kista - Stockholm


Signed:  **Date:** 13 April, 2021

Leif Mattsson

APPENDIX:

Reference No. SE-S-2100505

Technical Data:

<i>Type designation</i>	2379237-*, 1-2379237-*, 2379238-*, 1-2379238-*, 2379239-*, 1-2379239-*, 2379240-*, 1-2379240-*, 2359422-*, 1-2359422-*, 2359518-*, 1-2359518-*, 2359420-*, 2359421-*
<i>Rated voltage (V)</i>	500 VAC
<i>Rated current (A)</i>	Max 25A
<i>IP-Class</i>	IP68
<i>Number of terminals</i>	3
<i>Rated connecting cap</i>	1,5-4 mm ²
<i>Trademark</i>	
<i>Order number</i>	2102877
<i>Product information</i>	Rated currents for connectors: 16A with 1,5 mm ² / 20A with 2,5 mm ² / 25A with 4 mm ²

Product type references (not marked)

2379237-*: in-line female connector 2359418-1, screw terminals, cable gland 2363547-1 (11.0-15.0 mm)
 1-2379237-*: in-line female connector 2359418-1, screw terminals, cable gland 2363547-2 (7.0-10.0 mm)
 2379238-*: in-line male connector 2359419-1, screw terminals, cable gland 2363547-1 (11.0-15.0 mm)
 1-2379238-*: in-line male connector 2359419-1, screw terminals, cable gland 2363547-2 (7.0-10.0 mm)
 2379239-*: in-line female connector 2365125-1, crimp terminals, cable gland 2363547-1 (11.0-15.0 mm)
 1-2379239-*: in-line female connector 2365125-1, crimp terminals, cable gland 2363547-2 (7.0-10.0 mm)
 2379240-*: in-line male connector 2365129-1, crimp terminals, cable gland 2363547-1 (11.0-15.0 mm)
 1-2379240-*: in-line male connector 2365129-1, crimp terminals, cable gland 2363547-2 (7.0-10.0 mm)

2359422-*: panel mounted female connector 2359422-1, screw terminals
 1-2359422-*: panel mounted female connector 2359422-1, crimp terminals
 2359518-*: panel mounted male connector 2359518-1, screw terminals
 1-2359518-*: panel mounted male connector 2359518-1, crimp terminals

2359420-*: 3-way junction (1 male + 2 female), rated current max 25A
 2359421-*: 4-way junction (1 male + 3 female), rated current max 25A

“*” denotes polarization key (1 or 2)



APPENDIX:

Reference No. SE-S-2100505

Manufacturing Sites:

According to the principle of presumption of conformity, this certificate, which includes production control, constitutes support for an EC Declaration of Conformity and CE marking according to the Low Voltage Directive 2014/35/EU.

This presumption can expire before end of validity of this certificate due to new issued Standard or Amendment and changes within the EU legislation.

Certification Body: Intertek Semko AB, Product Certification **Place:** Kista - Stockholm

Signed:



Date: 13 April, 2021

Leif Mattsson

Intertek