


US-35679-A1-UL





US-35679-A1-UL

Ratings:

Model 1FBH3: 480 Vac, 50-60 Hz, 480 Vdc, 1 A, 90°C, 40/100/21. Model 2FBH3: 480 Vac, 50-60 Hz, 480 Vdc, 2 A, 90°C, 40/100/21. Model 3FBH3: 480 Vac, 50-60 Hz, 480 Vdc, 3 A, 90°C, 40/100/21. Model 5FBH3: 480 Vac, 50-60 Hz, 480 Vdc, 5 A, 90°C, 40/100/21.

Additional Information:

The original report was modified to include the following changes/additions: Modify Manufacturer's information, see test report.

Additionally evaluated to EN 60939-3:2015; National Differences specified in the CB Test Report.

Additional information (if necessary)



 \boxtimes

UL (US), 333 Pfingsten Rd IL 60062, Northbrook, USA

UL (Demko), Borupvang 5A DK-2750 Ballerup, DENMARK

UL (JP), Marunouchi Trust Tower Main Building 6F, 1-8-3 Marunouchi, Chiyoda-ku, Tokyo 100-0005, JAPAN UL (CA), 7 Underwriters Road, Toronto, M1R 3B4 Ontario, CANADA

For full legal entity names see www.ul.com/ncbnames

Date: 2020-07-10 Original Issue Date: 2020-04-28

Jolanda fr. W.e. Signature:

Jolanta M. Wroblewska