File E13288 Vol. 3

Sec. 1 Page 1 and Report

Issued: 1972-03-15 Revised: 2007-04-05

DESCRIPTION

PRODUCT COVERED:

Type "Plasti-Grip" terminals, butt, end and parallel connectors (22-10 AWG) .

Type "Solistrand" terminals, butt, and parallel connectors, (22-4/0 ANG).

Type "DG" (Diamond-Grip) terminal, butt and parallel connectors (22-la AWG) .

Type "PIDG" (preinsulated Diamond-Grip) terminals, butt and parallel connectors (22-10 AWG).

GENERAL CHARACTER AND USE:

General - The pressure terminal connectors may be provided with various sizes and shapes of the Tang. (such as ring, spade, hook, etc.)

Plasti-Grip - These devices are insulated pressure terminals and cable connectors designed for installation on wires by means of hand tools or press dies designated "P.I.D.G. for terminals and P.C. for splices". These connectors are rated 600 v max for building wire and 1000 volts for fixtures and signs in locations where the temperature does not exceed 90 degrees C. They are intended for use on a wire range of No. 22 to 10 AWG solid or stranded. The wire combinations for the parallel types are as follows:

Cat. No. 34136 (yellow)

Wire	- 1	No. of Addit	ional Wires	(One Size (Only)	
Size	No.	No. 18	No. 16	No. 14	No.12	No. 10
No. 18	1	3	2	1 to 2	1	1
	2	2	1 to 2	1 to 2	1	
	3	1	1			
No. 16	1	3	1 to 2	1 to 2	1	1
	2	1 to 2	1	1		
No. 14	1	1 to 3	1 to 2	1	1	
	2	1 to 2	1			
No. 12	1	1 to 2	1	1	1	
No. 10	1	1				

File E13288 Vol. 3 Sec. 1 Page 1A Issued: 1972-03-15 and Report Revised: 2011-03-16

Cat. No. 34134 (blue)

Wire		Number of	Additional 1	Wires	(One	Size	Only)	
Size	No.	No. 18					No.	16
No. 18	1	1				71		1
Na. 16	ī	ī						

Cat. Nos. 1-171512-0, 171512-2, 171512-4, 171512-6 or 171512-8 (Red)

Wire Size
22-18 Sol/Str
Wire Strip Length - 5.2 -6.0 mm

 $\underline{\text{Solistrand}}$ — These devices are uninsulated pressure cable connectors intended to be installed with the manufacturers solistrand Type W hind or power driven tools.

These connectors are Listed for a wire range of Nos. 22-4/0 AWG stranded wires and Nos. 22-14 AWG solid wires.

 $\underline{\text{Type DG (Diamond-Grip)}} \ - \ \text{These are pressure terminal and cable} \\ \text{connectors designed to be installed on wires by means of DG hand or power} \\ \text{tools on No. 22-10 AWG stranded copper wire.}$

Type PIDG (Preinsulated Diamond—Grip) — These are similar to the Diamond—Grip series except they are provided with insulation and are rated 300 V max, 105 oC max. Cat. No. 31885, of the Type PIDG is installed with PIDG hand tools on No. 22-16 AWG stranded copper wire, and power tooling an Nos. 22, 20, 18, 14, 12 and 10 stranded copper wire.

 $\underline{\text{Tooling}}$ — Typical tooling as illustrated shows the acceptable configuration of the dies. The form of handle or other constructional features is not specified.

INDEX FOR ILLUSTRATIONS:

Plasti-Grip, Solistrand, Diamond-Grip, and PIDG connectors are shown in Ill. 1 through 33 in accordance with the following tabulation.

Wire Range	Type of Connector	Ill. No.
22 AWG	PIDO	43
22-16 AWG	DG, PTDG, Ring Tongue	I
22-16 AWG	PG, Solistrand, Ring Tongue	- 2
22-16 AWG	DG, PIDO, Slotted Tongue	3
22-16 AWG	PG, Solistrand, Slotted Tongue	4
22-16 AWG	DG, PIDG, PC, Solistrand, Butt Parallel, Closed End Connectors	5
22-16 AWG	PG	40, 41
22-16 AWG	PTDG	43, 44
22-16 AWG	Solistrand	42

File E13288		3-15-72 3-27-85
Wire Range	Type of Connector	<u>Ill. No.</u>
16-14 AWG * *	DG, PIDG, Ring Tongue PG, Solistrand, Ring Tongue DG, PIDG, Slotted Tongue PG, Solistrand, Slotted Tongue DG, PIDG, PG, Solistrand, Butt, Parallel, Closed End Connectors PG PIDG	6, 10 7, 11 8 9 12
*	Solistrand	42
12-10 AWG *	DG, PIDG, Ring Tongue PG, Solistrand, Ring Tongue DG, PIDG, Slotted Tongue PG, Solistrand, Slotted Tongue DG, PIDG, PG, Solistrand, Butt, Parallel, Closed End Connector PG	13 14 15 16 17 s
8 AWG	Solistrand, Ring Tongue Solistrand, Flag, Parallel, Butt Connectors	18 19
*	Solistrand	42
6 AWG	Solistrand, Ring Tongue Solistrand, Flag, Parallel, Butt Connectors	20
*	Solistrand	42
4 AWG	Solistrand, Ring Tongue Solistrand, Flag, Parallel, Butt Connectors	22 23
*	Solistrand	42
2 AWG	Solistrand, Ring Tongue Solistrand, Flag, Parallel, Butt Connectors	24 25
1/O AWG	Solistrand, Ring Tongue Solistrand, Flag, Parallel, Butt Connectors	26 27
2/0 AWG	Solistrand, Ring Tongue Solistrand, Flag, Parallel, Butt Connectors	28 29
3/0 AWG	Solistrand, Ring Tongue Solistrand, Flag, Parallel, Butt Connectors	30 31
4/O AWG	Solistrand, Ring Tongue Solistrand, Flag, Parallel, Butt Connectors	32 33

J.T. N.M.