

B-138 Series, Rated up to 60 Amps, 115/200 VAC, 400 Hz

Product Facts

- TPST NO and TPDT NC
- Gasket sealed or Hermetically sealed
- 115/200 VAC, 400 Hz, 3 phase
- Auxiliary contacts available
- Meets the requirements of MIL-PRF-6106



Performance Data

Electrical Characteristics Contact Arrangement — TPST NO and TPDT NC Rated Operating Voltage — 115/200 VAC, 400 Hz, 3 phase Current, Resistive — 60 Amps Current, Inductive — 60 Amps Current, Motor — 60 Amps Current, Rupture — 600 Amps General Characteristics Temperature Range — -55°C to +71°C Operating Cycles (Life) at Rated Resistive Load, Min. — 50,000 cycles

Operating Cycles (Life) Mechanical, Min. — 100,000 cycles Dielectric Strength — All Circuits to Ground — 1,500 Vrms Circuit to Circuit — 1,500 Vrms Coil to Ground and Aux. Contacts — 1,000 Vrms

Altitude Max. — 50,000 ft. Weight, Nominal — 1.50 to 2.0 lbs


Coil Characteristics

Duty Cycle — Continuous or continuous with suppression Operating Voltage, Nom. — 28 Vdc

Pickup Voltage, Max. @ 85°C — 18 Vdc

Dropout Voltage, Max. — 1.5 to 7 Vdc Coil Current @ 29 Vdc Max. @ 25°C — 0.5 Amps Inrush — 5 Amps

Coil Type



For factory-direct application assistance, phone 419-521-9500 or fax 419-526-2749.

6–22

Catalog 5-1773450-5 Revised 3-13

m to change.


Dimensions are shown for reference purposes only. Specifications subject

Dimensions are in millimeters unless otherwise specified.

USA: +1 800 522 6752 Asia Pacific: +86 0 400 820 6015 UK: +44 800 267 666 For additional support numbers please visit www.te.com









Mounting Style A

Mounting Style B


Circuit Configurations (Consult factory for other available circuit configurations)




Circuit Configuration 1



Circuit Configuration 2



Circuit Configuration 3



Circuit Configuration 4

HARTMAN Part Number	Construction Type	Mounting Style	Coil Type	Circuit Config.	TE Part Number
B-138S	Gasket/Vented	В	В	2	1616002-5
B-138XEH	Gasket/Vented	А	С	4	1616028-3
B-138BH	Gasket/Vented	A	А	1	1616028-1
B-138XAH	Gasket/Vented	А	А	3	1616028-2

For factory-direct application assistance, phone 419-521-9500 or fax 419-526-2749.

Catalog 5-1773450-5 Revised 3-13

www.te.com

Dimensions are shown for reference purposes only. Specifications subject to change.

Dimensions are in millimeters unless otherwise specified.

USA: +1 800 522 6752 Asia Pacific: +86 0 400 820 6015 UK: +44 800 267 666

For additional support numbers please visit www.te.com

6-23