

RAYCHEM Tubing Products

RMW

Medium Wall, Polyolefin Heat-Shrinkable Tubing

Product Facts

- Withstands mechanical abuse for increased product reliability
- Highly resistant to impact and abrasion
- Installation is fast and easy
- Resistant to chemicals and moisture
- Adhesive-lined version provides a complete moisture-proof seal preventing corrosion of underlying components
- RoHS compliant



Applications

Medium wall, general purpose RMW tubing is specifically designed for use in a broad range of low-voltage applications. RMW is tough and flexible, making it particularly suited for the insulation and protection of cable joints as well as for cable repair. Uncoated RMW provides insulation and strain relief.

Adhesive-lined RMW also provides an environmental seal. RMW is a suitable choice for applications where maximum reliability and product performance, and simplified installation are required. Because RMW is heat-shrinkable, a minimum number of sizes are needed to cover a wide range of cables and splice diameters.

Installation

Minimum shrink temperature: 110°C [230°F] Minimum full recovery temperature: 125°C [257°F]

Operating Temperature Range

-55°C to 110°C [-67°F to 230°F]

Specifications/Approvals

Series	Raychem	
RMW	RMW SCD	

Available in:	Americas	Europe	Asia Pacific	

1-87



RAYCHEM Tubing Products

RMW (Continued)

Product Dimensions

	Inside Diameter		Recovered Wall Thickness**	
Size	Minimum Expanded as Supplied	Maximum Recovered After Heating	Minimum Jacket Wall	
10/3	10 [0.394]	3 [0.118]	1.0 [0.039]	
16/5	16 [0.630]	5 [0.197]	1.4 [0.055]	
25/8	25 [0.984]	8 [0.315]	2.0 [0.079]	
35/12	35 [1.378]	12 [0.472]	2.0 [0.079]	
50/16	50 [1.968]	16 [0.630]	2.0 [0.079]	
63/19	63 [2.480]	19 [0.748]	2.4 [0.095]	
75/22	75 [2.953]	22 [0.866]	2.7 [0.106]	
85/25	85 [3.346]	25 [0.984]	2.8 [0.110]	
95/29	95 [3.740]	29 [1.142]	3.1 [0.122]	
115/34	115 [4.528]	34 [1.339]	3.1 [0.122]	
140/42	140 [5.112]	42 [1.654]	3.1 [0.122]	
160/50	160 [6.299]	50 [1.968]	3.2 [0.126]	
180/60	180 [7.087]	60 [2.362]	3.2 [0.126]	
245/80*	245 [9.646]	80 [3.150]	2.4 [0.095]	
285/135	285 [11.220]	135 [5.315]	1.4 [0.055]	

Ordering Information

Color	Standard	Black (-0)	
Size selection	Always order the largest size that will shrink snugly over the component to be covered. Special order sizes available upon request.		
Standard packaging	1200mm lengths.		
Marking	Tubing will be marked with product name, size and batch number.		
Ordering description	Ordering description Specify product name, size, cut length, coating option (for example, RMW-10/3-1200 ADH = Adhesive-line, U = Uncoated).		

^{*}Uncoated only

**Wall thickness will be less if tubing recovery is restricted during shrinkage.