

TC Caps

Semirigid, Flame-**Retardant Polyolefin Caps**

Product Facts

- 2.5:1 shrink ratio
- Flame-retardant
- Permanent or temporary method to terminate wires
- Rapid, simple installation
- Rugged protection against abrasion, vibration, and flexing

Specifications/Approvals

RoHS compliant



Applications

Widely used for wire terminations because of their light weight, small size and durability. Vibration-proof caps are used to insulate and terminate dead-end electrical cables, fixtures, connectors, and other electrical equipment. Also used to protect the ends of wire during storage.

Installation

Minimum shrink temperature: 110°C [230°F] Minimum full recovery temperature: 135°C [275°F]

Operating Temperature Range

-55°C to 135°C [-67°F to 275°F]

Series	UL ှ	Raychem TC Caps SCD	
TC Caps	E85381 600 V, 125°C		





TC Caps (Continued)

Product Dimensions

	Color	L	.ength	Inside I	Diameter	Recovered Wall Thickness**
Size		Nominal Overall as Supplied	Minimum Open Barrel after Recovery*	Minimum Expanded as Supplied	Maximum Recovered After Heating	After Heating
TC 4001	White (-9)	19.1 (0.750)	10.2 (0.400)	1.6 (0.063)	0.8 (0.030)	0.51 ± 0.12 (0.020 ± 0.005)
TC 4003	Red (-2)	25.4 (1.000)	14.0 (0.550)	3.2 (0.125)	1.3 (0.050)	0.64 ± 0.12 (0.025 ± 0.005)
TC 4005	Gray (-8)	28.6 (1.125)	14.0 (0.550)	6.4 (0.250)	2.5 (0.100)	0.69 ± 0.12 (0.027 ± 0.005)

*See glossary for definition of "barrel". **Wall thickness will be less if tubing recovery is restricted during shrinkage.

Ordering Information

Color	Standard One color per size per the Product Dimensions table.
Size selection	Always order the largest size that will shrink snugly over the component to be covered.
Standard packaging	In pieces.
Ordering description	Specify product name, size and color (for example, TC-CAPS-4003-2).

1-122

9-1773447-9 CIS WR 08/2011

te.com

Dimensions are in inches and millimeters unless otherwise specified. Values in brackets are metric equivalents.

Dimensions are shown for reference purposes only. Specifications subject to change.

USA: 1-800-522-6752 Canada: 1-905-475-6222 Mexico: 52-55-1106-0800 L. & S. America: 54-11-4733-2200 Germany: 49-6251-133-1999 China: 86-400-820-6015 Japan: 81-44-844-8013 UK: 44-800-267-666