



4

3

2

1

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
1		NEW DRAWING	02MAR22	GSK RS



PART NUMBER	MATERIAL NAME
EN7839-000	CSJ-SR-3513
EN7840-000	CSJ-SR-3514
EN7841-000	CSJ-SR-3515

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -
MATERIAL -	FINISH -



DWN SATHISH KUMAR G 03MAR2022				
CHK RAMÓN SÁNCHEZ 03MAR2022				
APVD RAMÓN SÁNCHEZ 03MAR2022	NAME CSJ-SR Cold Applied Joint MEDIUM VOLTAGE			
PRODUCT SPEC -	SIZE A3	CAGE CODE 00779	DRAWING NO C-0149-CSJ-SR	RESTRICTED TO -
APPLICATION SPEC -	SCALE NTS		SHEET 1 of 2	REV 1
WEIGHT	CUSTOMER DRAWING			

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
-	-	SEE SHEET 1	-	-	-

PRODUCT SELECTION INFORMATION: DIMENSIONS IN INCHES (MM)

Description	Voltage Class	Nominal Cable Range	Min/Max Insulation OD	Max Jacket OD	Connector Dimensions Max. OD Max. Length	Kit Installed Length	Required Installation Space
CSJ-SR Joint without connector							
CSJ-SR-1513	15 kV	350 - 1000	1.03 - 1.58 (26.2 - 40.0)	2.05 (52.1)	1.65 (42.0) 6.69 (170.0)	33 (838)	43 (1090)
CSJ-SR-1514	15 kV	750 - 1250	1.28 - 2.05 (32.5 - 52.0)	2.60 (66.0)	1.85 (47.0) 7.90 (200.0)	37 (939)	49 (1244)
CSJ-SR-2813	28 kV	4/0 - 750	1.03 - 1.58 (26.2 - 40.0)	2.05 (52.1)	1.65 (42.0) 6.69 (170.0)	33 (838)	43 (1090)
CSJ-SR-2814	28 kV	500 - 1250	1.28 - 2.05 (32.5 - 52.0)	2.60 (66.0)	1.85 (47.0) 7.90 (200.0)	37 (939)	49 (1244)
CSJ-SR-3513	35 kV	1/0 - 350	1.03 - 1.49 (26.2 - 37.8)	2.05 (52.1)	1.40 (35.6) 5.50 (140.0)	33 (838)	43 (1090)
CSJ-SR-3514	35 kV	350 - 1000	1.36 - 2.05 (34.5 - 52.0)	2.60 (66.0)	1.96 (50.0) 7.90 (200.0)	37 (939)	49 (1244)
CSJ-SR-3515	35 kV	750 - 1500	1.63 - 2.36 (41.4 - 60.0)	2.60 (66.0)	2.36 (60.0) 7.90 (200.0)	37 (939)	49 (1244)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 03MAR2022 SATHISH KUMAR G		
DIMENSIONS: mm [INCHES]		CHK 03MAR2022 RAMÓN SÁNCHEZ		
		APVD 03MAR2022 RAMÓN SÁNCHEZ	NAME CSJ-SR Cold Applied Joint MEDIUM VOLTAGE	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC -	RESTRICTED TO -	
0 PLC ± -		APPLICATION SPEC -	SIZE A3	
1 PLC ± -		WEIGHT	CAGE CODE 00779	DRAWING NO 0149-CSJ-SR
2 PLC ± -		CUSTOMER DRAWING		
3 PLC ± -		SCALE NTS		
4 PLC ± -		SHEET 2 OF 2		
ANGLES ± -		REV 1		
MATERIAL -		FINISH -		