


LOC	DIST	P	LTR	REVISIONS	DATE	DRN	APPR
				ÄNDERUNGEN			
				BESCHREIBUNG			
				BESCHREIBUNG			
A1	-			EG00-1033-01	21JUN2001	NG	GF
PROJECT NO.: EG00-1033-01							

SIDE A: T01 FEMALE PLUG CONN.PANEL MNT.; SOLDER-VER. 3 POS.  
 SEITE A: T01 BUCHSENSTECKER; EINBAU; LÖTVERS. 3 POL.

SIDE B: AMPMODU RECEPTACLE CONNECTOR 4 POS.  
 SEITE B: AMPMODU BUCHSENSTECKER 4 POL.



WIRES RIPPED UP CA. 20 mm AT BOTH SIDES LEITUNGEN CA. 20 mm AN BEIDEN ENDEN AUFGETRENNT	5
STRANDED WIRE 3.0 mm ± 0.5 STRIPPED; COVERED WITH SHRINKABLE SLEEVE AFTER SOLDERING LITZENDRAHT 3.0 mm ± 0.5 ABISOLIERT DURCH SCHRUMPFSCHLAUCH NACH DEM LÖTEN GESCHÜTZT	4
CUTTING LENGTH OF WIRES / SCHNEIDLÄNGE DER LEITER: 190mm ± 5	3
CABLE TIE CONCENTRIC ATTACHED KABELBINDER MITTIG ANGEBRACHT	2
WIRE CRIMP SNAP-IN RECEPTACLE CONTACTS / LEITER-CRIMP-SNAP-IN BUCHSENKONTAKTE	1
TECHNICAL DATA TECHNISCHE DATEN	

TYCO-NO. / TYCO NR.	DESCRIPTION / BESCHREIBUNG	ITEM-NO. TEIL-NR.
1-1437720-2		
1	CABLE TIE / KABELBINDER 2.5 x 100 mm	7
1	WIRE: LIY 0.25 mm <sup>2</sup> COLOR: GREEN / LEITER: LIY 0.25 mm <sup>2</sup> FARBE: GRÜN	6
1	WIRE: LIY 0.25 mm <sup>2</sup> COLOR: BROWN / LEITER: LIY 0.25 mm <sup>2</sup> FARBE: BRAUN	5
1	WIRE: LIY 0.25 mm <sup>2</sup> COLOR: WHITE / LEITER: LIY 0.25 mm <sup>2</sup> FARBE: WEISS	4
3	HEAT-SHRINKABLE SLEEVE 24 UL, VPE-1-1, 2-sw; EACH 10mm ± 1 / SCHRUMPFSCHLAUCH 24 UL, VPE-1-1, 2-sw; JE 10mm ± 1	3
1	AMPMODU RECEPTACLE CONN. 4 POS. NO.:280359 WITH RECEPTACLE CONTACT NO.:280530-4 AMPMODU BUCHSENSTECKER 4 POL. NR.:280359 MIT BUCHSENKONTAKTEN NR.: 280530-4	2
1	T01 FEMALE PLUG CONN. PANEL MNT.; SOLDER-VERSION NO.: 9-1437719-6 / T01 BUCHSENSTECKER EINBAU; LÖTVERSION NR.: 9-1437719-6	1
QTY REQD PER ASSY	DESCRIPTION / BESCHREIBUNG	ITEM-NO. TEIL-NR.
T01-058M-S03		
CATALOG-NO.	PARTS-LIST / TEILELISTE	

GREEN / GRUEN	1	2
BROWN / BRAUN	2	3
WHITE / WEISS	3	1
-	-	4
COLOR OF WIRE / FARBE DER EINZELADER	A	B
PIN CONFIGURATION ANSCHLUSSBELEGUNG		

<small>THIS DRAWING IS A PROPERTY OF TYCO ELECTRONICS CORPORATION. IT IS TO BE USED ONLY FOR THE ORGANIZATION AND FOR THE PROJECT FOR WHICH IT WAS PREPARED. IT IS NOT TO BE REPRODUCED OR TRANSMITTED IN ANY FORM OR BY ANY MEANS, ELECTRONIC OR MECHANICAL, INCLUDING PHOTOCOPYING, RECORDING, OR BY ANY INFORMATION STORAGE AND RETRIEVAL SYSTEM, WITHOUT THE WRITTEN PERMISSION OF TYCO ELECTRONICS CORPORATION.</small>		DWN H. GELSTER 21JUN2001 CDR H. SCHERER 21JUN2001	NAME H. SCHERER 21JUN2001	Tyco Electronics AMP GmbH D - 64625 Bensheim
DIMENSIONS: MASSENHEITEN (MM)		TOLERANCES, UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN		APVD H. FEJLMEIJER 21JUN2001
MATERIAL -		FINISH/SCHREIBFÄRBE/FARBE -		PRODUCT SPEC. -
WEIGHT GEWICHT -		APPLICATION SPEC. VERARBEITUNGSSPEZ. -		SIZE A1
CUSTOMER DRAWING -		SCALE -		DRAWING NO. 1-1437720-2 SHEET 1 OF 1 REV A1