





| REVISIONS |         |             |               |           |            |
|-----------|---------|-------------|---------------|-----------|------------|
| P         | LTR     | DESCRIPTION |               | DATE      | DWN / APVD |
| J9        | REVISED | PER         | ECN-22-158799 | 15JUN2022 | RK / MF    |

- 1ASSEMBLIES MAY BE BROKEN TO DESIRED NO OF POSITIONS.
- 2BREAKAWAY NOTCH ANGLE CAN BE ORIENTED TO THE RIGHT (AS SHOWN) OR TO THE LEFT.
- 3.000100-.000200 MATTE TIN-LEAD OVER .000050 NICKEL.
- 4.000100-.000200 BRIGHT TIN OVER .000050 NICKEL.
- 5PRELIMINARY PART - NOT RELEASED FOR PRODUCTION.
- 6HOUSING MATERIAL: FLAME RETARDANT THERMOPLASTIC; COLOR-BLACK.
- 7.000100-.000200 MATTE TIN OVER .000050 NICKEL.
- 8OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



RECOMMENDED HOLE LAYOUT

|   |       |       |    |    |            |
|---|-------|-------|----|----|------------|
| 7 | 3.984 | 3.900 | 39 | 40 | 9-103329-0 |
| 7 | 3.884 | 3.800 | 38 | 39 | 8-103329-9 |
| 7 | 3.784 | 3.700 | 37 | 38 | 8-103329-8 |
| 7 | 3.684 | 3.600 | 36 | 37 | 8-103329-7 |
| 7 | 3.584 | 3.500 | 35 | 36 | 8-103329-6 |
| 7 | 3.484 | 3.400 | 34 | 35 | 8-103329-5 |
| 7 | 3.384 | 3.300 | 33 | 34 | 8-103329-4 |
| 7 | 3.284 | 3.200 | 32 | 33 | 8-103329-3 |
| 7 | 3.184 | 3.100 | 31 | 32 | 8-103329-2 |
| 7 | 3.084 | 3.000 | 30 | 31 | 8-103329-1 |
| 7 | 2.984 | 2.900 | 29 | 30 | 8-103329-0 |
| 7 | 2.884 | 2.800 | 28 | 29 | 7-103329-9 |
| 7 | 2.784 | 2.700 | 27 | 28 | 7-103329-8 |
| 7 | 2.684 | 2.600 | 26 | 27 | 7-103329-7 |
| 7 | 2.584 | 2.500 | 25 | 26 | 7-103329-6 |
| 7 | 2.484 | 2.400 | 24 | 25 | 7-103329-5 |
| 7 | 2.384 | 2.300 | 23 | 24 | 7-103329-4 |
| 7 | 2.284 | 2.200 | 22 | 23 | 7-103329-3 |
| 7 | 2.184 | 2.100 | 21 | 22 | 7-103329-2 |
| 7 | 2.084 | 2.000 | 20 | 21 | 7-103329-1 |
| 7 | 1.984 | 1.900 | 19 | 20 | 7-103329-0 |
| 7 | 1.884 | 1.800 | 18 | 19 | 6-103329-9 |
| 7 | 1.784 | 1.700 | 17 | 18 | 6-103329-8 |
| 7 | 1.684 | 1.600 | 16 | 17 | 6-103329-7 |
| 7 | 1.584 | 1.500 | 15 | 16 | 6-103329-6 |
| 7 | 1.484 | 1.400 | 14 | 15 | 6-103329-5 |
| 7 | 1.384 | 1.300 | 13 | 14 | 6-103329-4 |
| 7 | 1.284 | 1.200 | 12 | 13 | 6-103329-3 |
| 7 | 1.184 | 1.100 | 11 | 12 | 6-103329-2 |
| 7 | 1.084 | 1.000 | 10 | 11 | 6-103329-1 |
| 7 | .984  | .900  | 9  | 10 | 6-103329-0 |
| 7 | .884  | .800  | 8  | 9  | 5-103329-9 |
| 7 | .784  | .700  | 7  | 8  | 5-103329-8 |
| 7 | .684  | .600  | 6  | 7  | 5-103329-7 |
| 7 | .584  | .500  | 5  | 6  | 5-103329-6 |
| 7 | .484  | .400  | 4  | 5  | 5-103329-5 |
| 7 | .384  | .300  | 3  | 4  | 5-103329-4 |
| 7 | .284  | .200  | 2  | 3  | 5-103329-3 |
| 7 | .184  | .100  | 1  | 2  | 5-103329-2 |
| 7 | .084  | -     | -  | 1  | 5-103329-1 |

|            |   |       |       |    |    |            |
|------------|---|-------|-------|----|----|------------|
| OBSOLETE   | 4 | 3.984 | 3.900 | 39 | 40 | 4-103329-2 |
|            | 4 | .984  | .900  | 9  | 10 | 4-103329-1 |
|            | 3 | 3.984 | 3.900 | 39 | 40 | 4-103329-0 |
|            | 3 | 3.884 | 3.800 | 38 | 39 | 3-103329-9 |
|            | 3 | 3.784 | 3.700 | 37 | 38 | 3-103329-8 |
|            | 3 | 3.684 | 3.600 | 36 | 37 | 3-103329-7 |
|            | 3 | 3.584 | 3.500 | 35 | 36 | 3-103329-6 |
|            | 3 | 3.484 | 3.400 | 34 | 35 | 3-103329-5 |
|            | 3 | 3.384 | 3.300 | 33 | 34 | 3-103329-4 |
|            | 3 | 3.284 | 3.200 | 32 | 33 | 3-103329-3 |
| SUPERSEDED | 3 | 3.184 | 3.100 | 31 | 32 | 3-103329-2 |
|            | 3 | 3.084 | 3.000 | 30 | 31 | 3-103329-1 |
|            | 3 | 2.984 | 2.900 | 29 | 30 | 3-103329-0 |
|            | 3 | 2.884 | 2.800 | 28 | 29 | 2-103329-9 |
|            | 3 | 2.784 | 2.700 | 27 | 28 | 2-103329-8 |
|            | 3 | 2.684 | 2.600 | 26 | 27 | 2-103329-7 |
|            | 3 | 2.584 | 2.500 | 25 | 26 | 2-103329-6 |
|            | 3 | 2.484 | 2.400 | 24 | 25 | 2-103329-5 |
|            | 3 | 2.384 | 2.300 | 23 | 24 | 2-103329-4 |
|            | 3 | 2.284 | 2.200 | 22 | 23 | 2-103329-3 |
| OBSOLETE   | 3 | 2.184 | 2.100 | 21 | 22 | 2-103329-2 |
|            | 3 | 2.084 | 2.000 | 20 | 21 | 2-103329-1 |
|            | 3 | 1.984 | 1.900 | 19 | 20 | 2-103329-0 |
|            | 3 | 1.884 | 1.800 | 18 | 19 | 1-103329-9 |
|            | 3 | 1.784 | 1.700 | 17 | 18 | 1-103329-8 |
|            | 3 | 1.684 | 1.600 | 16 | 17 | 1-103329-7 |
|            | 3 | 1.584 | 1.500 | 15 | 16 | 1-103329-6 |
|            | 3 | 1.484 | 1.400 | 14 | 15 | 1-103329-5 |
|            | 3 | 1.384 | 1.300 | 13 | 14 | 1-103329-4 |
|            | 3 | 1.284 | 1.200 | 12 | 13 | 1-103329-3 |
| SUPERSEDED | 3 | 1.184 | 1.100 | 11 | 12 | 1-103329-2 |
|            | 3 | 1.084 | 1.000 | 10 | 11 | 1-103329-1 |
|            | 3 | .984  | .900  | 9  | 10 | 1-103329-0 |
|            | 3 | .884  | .800  | 8  | 9  | 103329-9   |
|            | 3 | .784  | .700  | 7  | 8  | 103329-8   |
|            | 3 | .684  | .600  | 6  | 7  | 103329-7   |
|            | 3 | .584  | .500  | 5  | 6  | 103329-6   |
|            | 3 | .484  | .400  | 4  | 5  | 103329-5   |
|            | 3 | .384  | .300  | 3  | 4  | 103329-4   |
|            | 3 | .284  | .200  | 2  | 3  | 103329-3   |
| OBSOLETE   | 3 | .184  | .100  | 1  | 2  | 103329-2   |
|            | 3 | .084  | -     | -  | 1  | 103329-1   |

|         |   |   |   |            |             |         |   |   |   |            |             |
|---------|---|---|---|------------|-------------|---------|---|---|---|------------|-------------|
| PLATING | C | B | A | NO OF POSN | PART NUMBER | PLATING | C | B | A | NO OF POSN | PART NUMBER |
|---------|---|---|---|------------|-------------|---------|---|---|---|------------|-------------|

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: INCHES

0. PLC ± -  
1. PLC ± -  
2. PLC ± -  
3. PLC ± .005  
4. PLC ± -  
ANGLES ± -

MATERIAL: POST: COPPER ALLOY

FINISH: SEE TABLE

DWN: J. MARTINELLI  
CHK: JOHN KNITTLE  
APVD: B. FLINCHBAUGH

16OCT92  
23NOV92  
23NOV92

NAME: ASSY,HDR,BREAKAWAY, MODII, SINGLE ROW, .100 C/L, RIGHT ANGLE, WITH .025 SQ POSTS

SIZE: A1

CAGE CODE: 00779

DRAWING NO: 103329

RESTRICTED TO: -

CUSTOMER DRAWING

SCALE: 4:1

SHEET: 1 OF 1

REV: J9