





.XXX = in
XX.X = mm

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
03 ₀	REVISED PER ECN 95-0042	1/27/95	<i>M.M.</i>



HOUSING	STAINLESS STEEL PER ASTM-A484 AND ASTM- A582, TYPE 303	PASSIVATE PER QQ-P-35
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM-B-196 OR ASTM-B-197, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204
COMPONENT	MATERIAL	FINISH
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES		
FRAC. ± 1/64	DEC. ±.005	ANGLES ± 1°
DRAWN BY SWA DATE 7/25/85		
CHECKED BY FN 8-2-85		
APPD BY DRG 8/2/85		
AMP Incorporated 140 Fourth Avenue Waltham, MA 02451-7599		
TITLE OSN JACK TO OSM JACK ADAPTER		
USE ASS'Y PROCEDURE		
NO. A.P. N/A		
SIZE B		
CODE IDENT NO. 26805		
3080-4010-02		
REV 030		
SCALE 3:1		
SHEET 1 OF 1		

NOTES:
1. MECHANICAL & ELECTRICAL REQUIREMENTS PER DEFENCE ELEC. SUPPLY CENTER SCD NO.85038, REV-