




NOTES:
1. CAPTURED CENTER CONTACT

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
01 ₀	RELEASED	4-11-91	<i>DRY</i>

HOUSING COUPLING NUT	STAINLESS STEEL PER ASTM-A484 AND ASTM-A582, TYPE 303	PASSIVATE PER ASTM-A380
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM B 196, ALLOY C17300, CONDITION H	GOLD PLATE PER MIL-G-45204 OVER COPPER PLATE PER MIL-C-14550
RETAINING RING	BERYLLIUM COPPER PER ASTM B 194, ALLOY C17200, CONDITION H	N/A
GASKET	SILICONE RUBBER PER ZZ-R-765	N/A
COMPONENT	MATERIAL	FINISH
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCE ON FRAC. DEC. ANGLES ± 1/64 ± .005 ± 1° DRAWN BY M.Y. DATE 4-5-91 CHECKED BY M.CATIZONE 4-11-91 APP'D BY <i>DRY</i> 4-11-91 These drawings and specifications are the property of Omni Spectra Incorporated and shall not be reproduced or copied or used in whole or in part as the basis for the manufacture or sale of item(s) without written permission.		
USE ASS'Y PROCEDURE		TITLE TNC TYPE A INTERFACE JACK TO OSM PLUG ADAPTER
NO. AP. N/A		SIZE B CODE IDENT NO. 26805 4182-2241-00 REV 01 ₀
SCALE 5:1		SHEET 1 OF 1