


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	19AUG2021	AP	IG
	A1	REVISED PER PCN-22-129536	10FEB2022	MK	DM




TE INTERNAL PN	ALIAS PN	PLATING
1060-16-0122-PS	1060-16-0122-PS	Ni/Cu Overall, Sn/Ni/Cu Wire Barrel
1060-16-0144-PS	1060-16-0144-PS	Selective Au, Ni/Cu Overall, Sn/Ni/Cu Wire Barrel
1060-16-0622-PS	1060-16-0622-PS	Ni/Cu Overall, Sn/Ni/Cu Wire Barrel
1060-16-0644-PS	1060-16-0644-PS	Selective Au, Ni/Cu Overall, Sn/Ni/Cu Wire Barrel
1060-16-1222-PS	1060-16-1222-PS	Ni/Cu Overall, Sn/Ni/Cu Wire Barrell
Y-1060-16-1244-PTS	1060-16-1244-PS	Selective Au, Ni/Cu Overall, Sn/Ni/Cu Wire Barrel

2. 100 TERMINALS PER STRIP

1. REFER TO PRODUCT DRAWINGS 1060-16-01XX, 1060-16-06XX AND 1060-16-12XX FOR PRODUCT DETAILS.

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. POLO 19AUG2021	 TE Connectivity					
DIMENSIONS: INCHES		CHK I. GRANTCHAROVA 19AUG2021						
	TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD I. GRANTCHAROVA 19AUG2021	NAME STAMPED CONTACT PIN SIZE 16 PARTIAL STRIP				
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.005 4 PLC ± ANGLES ±		PRODUCT SPEC 108-151000					
	MATERIAL		FINISH	APPLICATION SPEC 114-151000	SIZE A3	CAGE CODE 00779	DRAWING NO C-1060-16-XXXX-PS	RESTRICTED TO -
CUSTOMER DRAWING				WEIGHT	SCALE 6:1		SHEET 1 OF 1	REV A1