


LOC	DIST	REVISIONS				
AJ	00	P	LTR	DESCRIPTION	DATE	DWN
		B		REV PER ECO 070-027471	1/16/2008	JL



- NOTES:
- DESIGNED FOR USE WITH RG174/U, RG188/U AND RG316/U CABLE
 - CAPTURED CENTER CONTACT

1060174-1

PART NUMBER

HOUSING MOUNTING NUT CLAMP NUT INNER SLEEVE WEDGE WASHER	BRASS PER QQ-B-626 COMP. 360	GOLD PLATE PER MIL-G-45204 OVER COPPER PLATE PER MIL-C-14550
DIELECTRIC	TFE FLUOROCARBON PER ASTM-D-1457, MIL-P-19468, AND FED. SPEC L-P-403	N/A
CENTER CONTACT	BERYLLIUM COPPER PER ASTM B196, ALLOY 173	GOLD PLATE PER MIL-G-45204 OVER COPPER PLATE PER MIL-C-14550
LOCKWASHER	PHOSPHOR BRONZE PER QQ-B-750, GRADE B2 OR TIN BRASS PER ASTM-B-591	GOLD PLATE PER MIL-G-45204 OVER COPPER PLATE PER MIL-C-14550

COMPONENT	MATERIAL	FINISH
THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN RKS 12/30/68
	0 PLC ± -	CHK CW 1/15/90
	1 PLC ± -	APVD P.H 1/15/90
	2 PLC ± -	PRODUCT SPEC
	3 PLC ± .005	APPLICATION SPEC
	4 PLC ± -	408-04709
	ANGLES ± 1°	WEIGHT -
MATERIAL -	FINISH -	CUSTOMER DRAWING
CABLE ENTRY DIAMETER MINIMUM		SIZE A2
CONTACT .023	INNER SLEEVE .062	CAGE CODE 00779
CLAMP NUT .112		DRAWING NO 1060174-1
		RESTRICTED TO -
		SCALE 1:1
		SHEET 1 of 1
		REV B