



© COPYRIGHT 1981 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
✓	✓	0		DRAWN PER 5463	1-27-81



1. FOR APPLICATION IN .093/.125 THK. P.C. BOARDS
 2. POST DIAGONAL .0315/.0345 [0.80/0.88]
 3. COMPLIANT SECTION (SEE DETAIL)
 4. ALL DIMENSIONS ARE REFERENCE UNLESS OTHERWISE NOTED
- △ NICKEL PLATE .000100 MIN. THK.
△ GOLD PLATE .000300 MIN. THK. OVER NICKEL PLATE
△ SOLDER PLATE .000100 MIN. THK. OVER NICKEL PLATE

REEL NO. 118766-6		3.250 [82.55]	27	118815-1
A		POS	PART NO	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± .005 ANGLES ± 1°		CONTRACT NO		
MATERIAL CDA COPPER ALLOY 725		DR <i>Craig Pierce</i> 1/27/80		
FINISH NICKEL PLATE PER QQ-N-290 GOLD PLATE PER MIL-G-45204		CHK		
APPD		NAME		
APPD		COMB CONTACT - AMP PACE (.125 x .125) (HIGH GAPPING)		
DSGN APPD		SIZE CODE IDENT NO DRAWING NO		
OTHER APPD		C 00779 118815		
SCALE		SHEET		