


REVISIONS						
P	F	ZONE	LTR	DESCRIPTION	DATE	APPROVED
✓	✓		0	DRAWN PER 5463	CP 1-27-94	



- [2.36/3.18]
1. FOR APPLICATION IN .093/.125 THK. P.C. BOARDS
 2. POST DIAGONAL .0315/.0345 [0.80/0.88]
 3. COMPLIANT SECTION (SEE DETAIL)
 4. ALL DIMENSIONS ARE REFERENCE UNLESS OTHERWISE NOTED
 5. NICKEL PLATE .000100 MIN. THK.
 6. GOLD PLATE .000300 MIN. THK. OVER NICKEL PLATE
 7. SOLDER PLATE .000100 MIN. THK. OVER NICKEL PLATE

		3.250	82.55	Z7	118821-1
		REEL NO. 118753-6		A	POS
				PART NO	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ± — ANGLES ± —		CONTRACT NO DR <i>Craig Pierce 1-28-81</i> CHK		AMP AMP INCORPORATED Harrisburg, Pa.	
MATERIAL CDA COPPER ALLOY 725		APPD APPD		NAME COMB CONTACT-AMP PACE (.125 x .125) (LOW GAPPING)	
FINISH NICKEL PLATE PER QQ-N-290 GOLD PLATE PER MIL-G-45204		DSGN APPD OTHER APPD		SIZE C	CODE IDENT NO 00779
				DRAWING NO 118821	
				SCALE —	SHEET —