






Tailles 19 - 27 - 37 - 61



Tailles 03 - 07 - 12



Taille **	Ø A max.	Ø B UNEF 2B	C max.	Ø D mini Maxi
03	16,55	9/16" - 24	18,20	4,40 5,50
07	21,05	3/4" - 20	24,40	6,00 9,45
12	24,55	7/8" - 20	26,20	9,40 12,85
19	28,05	1" - 20	30,10	11,00 14,45
27	29,55	1"1/16 - 18	33,10	15,00 18,50
37	32,55	1"3/16 - 18	33,20	17,00 20,45
61	40,55	1"1/2 - 18	41,60	22,00 25,45

Matériau : acier inoxydable passivé

FT 119 0244 +- -b



Division Connecteurs Aéronautiques
TE, rue LAUDIER - BP 417 - 27081 EPREUX CEDEX 08 - FRANCE

FICHE TECHNIQUE
TECHNICAL DATA SHEET

204-119-C/01

b	11/08/2017	CE142717
d	14/11/2016	CE101116
Revision	Date	Observations

SERIE DCIN
Raccord droit

DATE 11/08/2017
REF : 119-0244-XX

VSA
Creation
Quintus
VSA
Approbation

VERSION : REVISION

Ce document est la propriété de CED et ne peut être reproduit ou communiqué sans son autorisation. This document is the property of CED and cannot be reproduced or disclosed without the CED approval.