


© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
✓	✓	0		DRAWN	5-7-82
					APPROVED JB



DEVELOPMENT ENGINEERING CONTROLLED


THIS PART IS FOR LIMITED PRODUCTION ONLY.
ABILITY TO PRODUCE IN CONTINUOUS PRODUCTION QUANTITIES FOR VARIOUS
CUSTOMERS APPLICATIONS IS NOT IMPLIED BY THIS LIMITED RELEASE.

NOTES

- △ COMPLIANT SECTION (SEE DETAIL)
- △ SOLDER PLATE .000030 MIN THK
- △ GOLD PLATE .000075 MIN THK
- △ NICKEL PLATE .000050 MIN THK
- △ SOLDER PLATE .000030 MIN THK
- △ SOLDER PLATE .000030 MIN THK

ALL DIMENSIONS IN []
ARE METRIC

- 7. POST DIAGONAL .0315 / .0345
- 8. FOR APPLICATION IN .093 / .125 THK
PC. BOARDS.



REEL NO 119517-2	1.300 [33.02]	.750 [19.05]	2.375 [60.235]	20	119512-1
	C	B	A	POS'N	PART NO
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.005 ANGLES ±2°	CONTRACT NO DR BILLMAN 10-16-81 CHK	AMP INCORPORATED Harrisburg, Pa.			
MATERIAL COPPER ALLOY 725	APPD APPD	NAME DOUBLE DENSITY (INNER CONTACT) COMB			
FINISH NOTE 1,2,3,4,5,6 AL PL PER MIL-G-45204 NI PL PER QQ-N-290	DSGN APPD OTHER APPD	SIZE C	CODE IDENT NO 00779	DRAWING NO 119512	SHEET 1-1