


© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA.
ALL INTERNATIONAL RIGHTS RESERVED. AMP INCORPORATED PRODUCTS
COVERED BY U. S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.

LOC DIST
AD 44

REVISIONS					
P	F	ZONE	LTR	DESCRIPTION	DATE
✓	✓	10		DRAWN	182
					JB




NOTES

- ▲ COMPLIANT SECTION (SEE DETAIL)
- ▲ SOLDER PLATE .000030 MIN THK
- ▲ GOLD PLATE .000075 MIN THK
- ▲ NICKEL PLATE .000050 MIN THK
- ▲ SOLDER PLATE .000030 MIN THK
- ▲ SOLDER PLATE .000030 MIN THK

7. POST DIAGONAL .0315 / .0345

B. FOR APPLICATION IN .093 / .125 THK P.C. BOARDS.

ALL DIMENSIONS IN []
ARE METRIC

DEVELOPMENT ENGINEERING CONTROLLED

THIS PART IS FOR LIMITED PRODUCTION ONLY.
ABILITY TO PRODUCE IN CONTINUOUS PRODUCTION QUANTITIES FOR VARIOUS CUSTOMERS APPLICATIONS IS NOT IMPLIED BY THIS LIMITED RELEASE.

REEL NO 119519-2	1.300 [33.02]	730 [19.05]	2.375 [60.235]	20	119514-1
	C	B	A	POS'N	PART NO
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON: DECIMALS ±.005 ANGLES ±2°	CONTRACT NO DR BILLMAN 10-16-81 CHK	AMP AMP INCORPORATED Harrisburg, Pa.			
MATERIAL BE CU 172	APPD <i>J. Cartham 5-7-82</i> APPD	NAME DOUBLE DENSITY (SHORTING CONTACT) COMB			
FINISH NOTE 1,2,3,4,5,6 AL PL PER MIL-G-45204 NI PL PER QQ-N-290	DSGN APPD OTHER APPD	SIZE C	CODE IDENT NO 00779	DRAWING NO 119514	
		SCALE			SHEET 1-1