




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	K1	REVISED PER ECR-25-242347	26APR2025	AG	DH


- 1
- CONTINUOUS STRIP ON REELS.
- 2
- MATING TAB THK TO BE 0.81 ± 0.025 [.032±.001].
- 3
- WIRE SIZE IS [#24-#20] AWG.
- 4
- INSULATION RANGE IS 1.27-2.03 [.050-.080] DIA.



VIEW A-A
SCALE 8:1



SECTION B-B
SCALE 8:1




SECTION C-C
SCALE 8:1

OBSOLETE

-	1217281-3
MATTE-TIN	1217281-2
0.002032 [.000080] MIN TIN	1217281-1
FINISH	PART NO.

F	2.29 [.090]	3.96 [.156]	F	1.40 [.055]	1.02[.040] [#20]	[#20]
					0.91[.036] [#22]	[#22]
					0.84[.033] [#24]	[#24]
TYPE	WIDTH	STRIP LENGTH ±0.38 ±[.015]	TYPE	WIDTH	±.051[±.002] HEIGHT	WIRE
INSUL BARREL CRIMP			WIRE BARREL CRIMP			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 29NOV99	TE Connectivity							
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± 0.38 [.015] 3 PLC ± - 4 PLC ± - ANGLES ± -	CHK MS FEHER 29NOV99								
		APVD D BRATINA 29NOV99								
		NAME RECEPTACLE, FASTIN-FASTON, 2.79 [.110] SERIES -								
MATERIAL BRASS		FINISH SEE TABLE		PRODUCT SPEC -	APPLICATION SPEC 114-2065	SIZE A3	CAGE CODE 00779	DRAWING NO C-1217281	RESTRICTED TO -	
				WEIGHT 0.000000			CUSTOMER DRAWING			
							SCALE 5:1	SHEET 1 OF 1	REV K1	