




MATERIALS:
SHELLS: BRASS PER QQ-B-626.
CONTACT: BERYLLIUM COPPER PER QQ-C-530.
DIELECTRICS: PTFE PER ASTM-D-1710.
JAM NUT: BRAS PER QQ-B-626.
LOCKWASHER: PHOSPHOR BRONZE PER QQ-B-750.
END CAP: BRASS PER QQ-B-626.

FINISHES:
CONTACT: GOLD PLATE PER MIL-G-45204.
SHELLS: NICKEL PLATE PER QQ-N-290.
JAM NUT: NICKEL PLATE PER QQ-N-290.
LOCKWASHER: NICKEL PLATE PER QQ-N-290.
END CAP: NICKEL PER QQ-N-290.

3. JAM NUT AND LOCKWASHER, NOT SHOWN, ARE BULK PACKAGED.



RECOMMENDED PCB CONFIGURARTION

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	0.13 [.005]
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH		

DWN
B. MOYER
28JAN99

CHK
B. MOYER
28JAN99

APVD
B. MOYER
28JAN99

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE Connectivity

JACK, RTANG, REV POLARITY
PCB, 50 OHM, SMB

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A2	00779	C=1274265	-

SCALE	SHEET	REV
8:1	1 of 1	D1