# SAFETY ORGANIZATIONS

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

UL RECOGNIZED: UL 1283 CSA CERTIFIED: CSA C22.2 No. 8 VDE APPROVED: EN 60939-2

#### OPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 130 AMP 277 VAC LINE TO GROUND

130 AMP 480 VAC PHASE TO PHASE

LINE FREQUENCY:

50-60Hz

MAXIMUM LEAKAGE CURRENT,

EACH LINE TO GROUND:

30 mA @ 277VAC 50 HZ

OPERATING AMBIENT TEMP. RANGE: ~10°C TO  $\pm 50$ °C @ RATED CURRENT, Ir. IN AN AMBIENT, To, HIGHER THAN 50°C, THE MAXIMUM OPERATING

CURRENT, I<sub>D</sub>, IS AS FOLLOWS:

 $I_0 = I_r \sim \sqrt{\frac{100 - T_0}{50}}$ 

### RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: -40°C TO +85°C HUMIDITY: 21 DAYS # 50°C 95% RH. CURRENT OVERLOAD TEST: 6 TIMES 1r FOR 8 SECONDS

CUSTOMER DRAWING
CATALOG # 130BCF6
ECR# APPRVD DATE
15-011624 TAM 08DEC15

# TEST SPECIFICATIONS:

INDUCTANCE: .55 mH NOMINAL

CAPACITANCE: (MEASURED @ 1KHz, 0.250VAC MAX., 25°C±1°C)

LINE TO GROUND: LINE TO LINE:

2.17 μF±20% 6.60 μF±20%

DISCHARGE RESISTOR: NO DISCHARGE RESISTOR:

660K A 6000MA (MIN.) 100VDC.


20°C AND 50% RH@

### RECOMMENDED RECEIVING INSPECTION HIPOT:

LINE TO GROUND: 1850 VDC FOR 1 MINUTE LINE TO LINE: 1850 VDC FOR 1 MINUTE

#### FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



50 ~ 50 ~ (TYPICAL) INSERTION LOSS														S 138-702 SPECIFICATION FOR HAZARDOUS SUBSTANCES
FREQUENCY WHz	.01	.03	.05	.10	.15	.30	.50	1.0	3.0	5.0	10	30	UNLESS OTHERWISE SPECIFIED TOLERANCE TO BE ±0,64 [±0,025] MATERIAL & FINISH; AS SUPPLIED	<b>ETE</b> TE Connectivity
q8 COMMON	11	26	35	48	55	78	83	67	49	40	29	15	NOTES:	CUSTOMER DRAWING
DIFF.	27	37	40	38	53	75	80	64	54	50	47	30		TE PART NO.: 3-1609091-2
A A	HOZO A	) (C	9)	THIS INCOMITION IS COMPRENITIAL AND PROPRIETRY TO TYCH ELECTRONICS CORPORATION AND ITS WORKINGE SLISSINGHES AND FIRLIBLE. IT MAY NOT BE DISCUSSED TO ANYONE DIMER THAN TYCH ELECTRONICS PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TYCH ELECTRONICS CORPORATION.							TES. IT Sonnei.	HAY NOT	1308CF6-A.ckd	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$