




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	ECN	DATE	DWN APVD
J	-		0	RELEASED	FJ00-0406-99	21/JUL/99	MH SM
			A	REVISED	FJ00-2077-99	17/DEC/99	MH IH
			B	REVISED	FJ00-0170-00	7/FEB/00	MH SM
			C	REVISED	FJ00-0790-00	2/JUN/00	MH SM
			D	REVISED	FJ00-1118-00	10.AUG.00	MH S.M

-1 : AS SHOWN
-1 : 本 ☒






推奨パネルカット寸法 t=1.6
RECOMMENDED PANEL LAYOUT t=1.6




THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		OWN M. HIGO 17 JUL '99	
DIMENSIONS: 単位: 英 mm		CHK S. MANABE 21 JUL '99	
TOLERANCES UNLESS OTHERWISE SPECIFIED 一般公差 10mm : ± 0.2 30mm : ± 0.25 100mm : ± 0.3 ANGLE : $\pm 0.3^\circ$		APVD S. MANABE 21 JUL '99	
MATERIAL 材料 熱可塑性樹脂		PRODUCT SPEC 製品規格 108-5659	
FINISH 仕上 -		APPLICATION SPEC 取付適用規格 114-5258	
		WEIGHT 30g	
CUSTOMER DRAWING		WIRE RANGE 包合電線断面積 -	
		INSULATION DIA 被覆外径 -	
		AMP タイコ エレクトロニクス アンプ株式会社 Kawasaki, Japan	
		NAME 名称 パネルマウント タイプ タブ ハウジング 50P <ダイナミック D-2000 ドロウ タイプ> PANEL MOUNT TYPE TAB HSG 50P <DYNAMIC D-2000 DRAWER TYPE>	
		SIZE A3	
		CAGE CODE 00779	
		DRAWING NO 番号 1318578	
		RESTRICTED TO -	
		SCALE 尺度 2-1	
		SHEET 1 OF 2	
		REV D	

-2: AS SHOWN
-2: 本図

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	ECN	DATE
J	-					
SEE SHEET 1 OF 2						



推奨パネルカット寸法 t=1.6
RECOMMENDED PANEL LAYOUT t=1.6
列番号 ROW ID



SECT A-A

注記:


1. 型番 1376059-1, 締付けトルクレンジ: 39.2~68.6N/cm (4~7kgf/cm)

NOTES:

1. 1376059-1, BINDING TORQUE RANGE: 39.2~68.6N/cm (4~7kgf/cm)

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:
単位: 概 mm



MATERIAL
材料 熱可塑性樹脂

TOLERANCES UNLESS OTHERWISE SPECIFIED

一般公差
10% : ±0.2
30% : ±0.25
100% : ±0.3
ANGLE : ±0.3°

FINISH
仕上 -

OWN 17 JUL '99

CHK 21 JUL '99

APVD 21 JUL '99

S. MANABE

S. MANABE

PRODUCT SPEC

製品規格

108-5659

APPLICATION SPEC

取付適用規格

114-5258

WEIGHT

30g

CUSTOMER DRAWING

WIRE RANGE 包合電線断面積	INSULATION DIA 被覆外径
-	-

AMP タイコ エレクトロニクス アンパ株式会社
Kawasaki, Japan

NAME
名称 パネルマウント タイプ タブ ハウジング 50P
<ダイナミック D-2000 ドロワ タイプ>
PANEL MOUNT TYPE TAB HSG 50P
<DYNAMIC D-2000 DRAWER TYPE>

SIZE	CAGE CODE	DRAWING NO	REV
A3	00779	1318578	-

SCALE 尺度	SHEET 2-1	OF 2	REV D
-------------	--------------	---------	----------

参考図面