


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	F	REVISED PER ECR-22-144422	01MAR2023	LP	DSC



AMP
WIRE RANGE

4 AWG
SOLID OR STRANDED

- 1 STAMP AMP 4 APPROX AS SHOWN
2. MATERIAL THK: 1.778±0.076[.070±.003]
- 3 MATERIAL:
COPPER PER ASTM B152, ANNEALED
- 4 FINISH:
TIN PLATE 0.00254[.000100] MIN EXT THK PER ASTM B545

100	LOOSE PIECE	132102-1
QTY	PACKAGE TYPE	PART NO.

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMS

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER
1-800-522-6752

FOR APPLICATION
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142

MAX RECOMMENDED OPERATING
TEMPERATURE:
170°C [338°F]

VOLTAGE RATING:
N/A

CIRCULAR MIL AREA:
16.8-26.7mm² [33,100-52,600] CIR MILS
SOLID OR STRANDED

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL

3

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± 0.127[.005]

4 PLC ± -

ANGLES ±

FINISH

4

DWN
G. ROBERT
19 09 89

CHK
G. ROBERT
04-MAR-97

APVD
-

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT

CUSTOMER DRAWING

SCALE
2:1

SHEET
1 OF 1

REV
F

TE Connectivity

NAME
TERMINAL, SOLISTRAND,
RING TONGUE, WIRE SIZE: 4 AWG

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-132102

RESTRICTED TO
-