

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20


BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC  
EDIST  
B

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
1		FIRST ISSUE	21DEC00	RC	JJ
A1		ECR-06-022445	20SEP06	MK	CN

ITEM NO	PART NUMBER	DESCRIPTION	QTY/ ASSY
1	1-1337544-0	50 ohm BNC ELBOW PLUG	2
2	1337767-1	STRAIN RELIEF	2
3	1337715-1	RG58C/U CABLE	A/R



1500 ±25	1337773-4
1000 ±25	1337773-3
500 ±12	1337773-2
250 ±10	1337773-1
DIM 'A'	AMP PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION  
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION  
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:  
MMTOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±0.1
2 PLC	±0.01
3 PLC	±0.001
4 PLC	±0.0001
ANGLES	±-

MATERIAL

-

FINISH

-

DWN 21DEC2000

R.CHURCHILL

CHK 21DEC2000

D.CHICK

APVD 21DEC2000

J.JEWELL

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING

AMP of Great Britain Ltd,  
Stannore, Middlesex, HA7 4RS.

NAME

BNC PLUG - BNC PLUG  
CABLE ASSEMBLY

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=1337773

SCALE NTS

SHEET 1

OF 1

REV A1