



WARNING - THIS DOCUMENT CONTAINS TECHNOLOGY WHOSE EXPORT IS RESTRICTED BY THE EXPORT ADMINISTRATION REGULATIONS ("EAR") PURSUANT TO 15 C.F.R. PARTS 730-774. VIOLATIONS OF THE EAR ARE SUBJECT TO SEVERE CRIMINAL PENALTIES UNDER THE EXPORT CONTROL REFORM ACT, AS AMENDED (TITLE 50, U.S.C., SEC. 4801, ET SEQ.).

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	ECR-06-023739	07SEP2006	MJG	JA
	C	REVISED PER ECN-24-284659	25SEP2024	PE	JG



- NOTES:
- FOR USE WITH FILECA CABLE 1703/4.
 - INSTRUCTION SHEET 408-1799-1.

COMPONENT	MATERIAL	FINISH
FRONT SHELL	BeCu PER ASTM B196	SILVER PLATE PER ASTM B700
SHELL	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
DIELECTRIC	PTFE FLUOROCARBON PER ASTM-D-1457	N/A
COLLAR	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
GASKETS	SILICONE RUBBER PER A-A-59588	N/A
SPRING	BeCu PER ASTM B194	TIN PLATE PER ASTM B545
WASHER	BRASS PER ASTM B36	SILVER PLATE PER ASTM B700
MALE CONTACT	BRASS PER ASTM B16	GOLD PLATE PER ASTM B488 OVER NICKEL PLATE PER SAE-AMS-QQ-N-290
SPACER	PTFE FLUOROCARBON PER ASTM-D-1457	N/A
SHELL	BRASS PER ASTM B16	SILVER PLATE PER ASTM B700
CRIMP FERRULE	COPPER OR BRASS ALLOY ROCKWELL B 45 MAX	SILVER PLATE PER ASTM B700



69493	69710-1	134004-1
DIE SET	CRIMP TOOL	ASSY PART NUMBER
1	FERRULE	3
1	CRIMP END ASSEMBLY	2
1	PLUG ASSEMBLY BNC	1
-1	DESCRIPTION	ITEM NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M GREENER 07SEP2006	TE Connectivity			
DIMENSIONS: mm		CHK J AMBROSE 07SEP2006				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD J AMBROSE 07SEP2006	NAME COAXION RF BNC TYPE 'E' PLUG CONNECTOR			
0 PLC ± 1 PLC ±0.5 2 PLC ±0.5 3 PLC ±0.5 4 PLC ± ANGLES ±1°		PRODUCT SPEC -	SIZE A200779			
MATERIAL -		APPLICATION SPEC -	CAGE CODE C-134004			
FINISH -		WEIGHT -	DRAWING NO C-134004			
		CUSTOMER DRAWING	SCALE 5:1		SHEET 1 OF 1	REV C