


LOC	DIST	REVISIONS				
P	LTR REV	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.	
FH	2	0	CREATION	14/09/99	JB AD	
		A	DRAWING UPDATE	09/10/08	LP GN	
		B	ECR-14-006085	24/04/14	JB GN	



MARKING: LOGO.REFERENCE,TORQUE,WIRE RANGE,BATCH N°

note: unloosen bolt, screw and breaking shear head element.

CAPACITIES						DIMENSIONS				
PN	REFERENCE	MAIN (mm <sup>2</sup> )		TAP (mm <sup>2</sup> )		BOLT	NOMINAL TORQUE (N.m)	MASS (Kg)	Package	Made in
		mini	maxi	mini	maxi					
1351231-2	DZ6UL-F CHINA	120	240	25	120 (150)	M10	40	0,300	50	CHINA
1351231-1	DZ6UL-F GECOL	120	240	25	120 (150)	M10	40	0,300	25	FRANCE

( ) : geometrically allowed

Connectors for use on live line



Closed side

RELEASED FOR PUBLICATION  
BY AMP INCORPORATED. ALL RIGHTS RESERVED. TOUS DROITS RESERVES.  
THIS DRAWING IS UNPUBLISHED. DIFFUSION RESENTE AMP  
COPYRIGHT 19

DIMENSIONS: mm	DWN /DESSINE L PETRIGNET	09/10/08	MATERIAL MATIERE	-	FINISH FINITION	-		
	CHK /VERIFIE A GUICHARD	-	<b>TE connectivity</b> <b>SIMEL PRODUCTS</b>					
TOLERANCES UNLESS OTHERWISE SPECIFIED PER TOLERANCES NON SPECIFIEES SELON :-	APVD /APPROUVE G NEDELLEC	-						
	PRODUCT SPEC SPEC. PRODUIT	-	NAME TITRE	DZ UL-F...				
	APPLICATION SPEC SPEC. APPLICATION	-	SIZE FORMAT	A4	CAGE CODE	00779		
	WEIGHT MASSE APPROX.	300g	DRAWING NO No PLAN	© =1351231				
CUSTOMER DWG / PLAN CLIENT			UNIQUEMENT POUR REFERENCE	SCALE ECHELLE	1:1	SHEET FEUILLE	1 OF 1 DE 1	REV B