



CUSTOMER DRAWING

## DRAWING NUMBER - 1385055 SHEET 2 OF 2 REV. A1

1	1 0		KEP	<u>e</u> 1	AIR FFFD	/home/	/amp182/	46
1	LEADMAKER & Bench model g				AIR FEED			Б
2		ICH M			AIR FEED			38509
4	1	_	_	С	692655-5	AIR FEED VALVE ASSY	70 69	00 M
4	1	1	_	A	461690-2	SPACER, AIR FEED	68	<u></u>
	REF	-	-	A	24042-2	VALVE, SHUT OFF	67	Þ
4	REF	-	-	С	692655-6	AIR FEED VALVE ASSY	66	Γ
4	1	1	-	В	2-460277-1	AIR FEED ASSY (1 INCH)	65	D
	2	2	-	A	4-21000-3	SCR,SHC (10-32×2.00)AIR ASS		
	-	1	-	A	980285-2	ELBOW, SWIVEL 1/8 NPT - 1/4 T	63	
	-	1	– IN	A	23238-1	QUICK DISCONNECT	62	
	-	12.00	IN	A	27319-4	TUBING, POLY-FLO Ø.25	61 60	
	1	1		С	454220-1	CAP, RAM	59	
	1	1	-	D	453736-1	HOUSING	58	
							57	
							56	
							55	
4							54	
	1	1	-	В	1-460680-0	FEED FINGER ASSY	53	
							52	
							51 50	
							50 49	
	_	1	_	A	22374-7	VALVE, QUICK EXHAUST	49	1
	-	1	-	A	22304-1	NIPPLE, HEX 1/8 NPT	47	1
							46	
	1	1	-	A	690191-1	PLUG, NYLON	45	
	1	1	-	С	455674-1	RAM	44	
	1	1	-	A	690125-1	WASHER, LAMINATED	43	С
	1	1	-	A	1-690124-3	WASHER, RAM	42	
	1	1	-	A	7-21002-9	BOLT, CRIMPER(5/16-24×1.00)	41	
							40 39	
	1	1	_	A	690223-2	SPACER, INSULATION DISC	38	
	1	1	_	D	354777-1	WIRE DISC, PLASTIC	37	
	1	1	-	A	22480-5	WASHER, SPRING	36	
	1	1	-	В	690212-1	POST, RAM	35	1
							34	
							33	
							32	Q.
							31	
							30 29	
	1	1	_	В	3-690451-2	SPACER, STRIPPER	28	
	1	1	_	A	240639-1	STRIPPER	27	
	1	1	-	D	455676-1	PLATE, BASE	26	
	2	2	-	A	22354-8	DRAG, STUD	25	1
	1	1	-	В	1-455678-5	PLATE, STRIP GUIDE	24	
							23	
	2	2	-	A	4-22281-1	SPRING, DRAG	22	
	1	-				DD10 ST00K	21	В
	1	1	-	AB	454177-1 458030-4	DRAG, STOCK GUIDE, STRIP (REAR)	20 19	
	1	1	_	C	458031-4	GUIDE, STRIP (REAR)	18	
				Ŭ	130031 1	COTEE, SHAT CHORTS	17	
							16	
							15	1
							14	
							13	
2	1	1	-	B	683661-1	BENDING TOOL	12	
<u> </u> }	1	1	-	B	1-240644-6	PLATE, REAR SHEAR	11	-
5	2	2	-	C	1-240645-2	SPACER, SHEAR PLATE	10 9	
1	1	1	-	B	1-240642-9	PLATE, FRONT SHEAR		
2	1	1	_	B	240654-3 2-240651-0	ANVIL Blade, slug	8	
1	1	1			E E 17001 V	JENDE, JEOU	6	1
	1	1	-	С	240641-3	SPACER, SLUG BLADE	5	1
							4	1
							3	
							2	
/	1	1	-	C	456428-2	CRIMPER, WIRE	1	
	-2	- 1	U/M	DWG SIZE	PART NO	DESCRIPTION	ITEM NO	
		DED A	201	-	- REVISION OF EACH A	SSY NO (WHEN BLANK, USE DWG REVIS	I ON)	A
-	DEAR	LER V		MATL	_ HT TR	PARTS LIST		1
QTY	′ REQD SIONS	IN INC		1	_			
QTY 1ENS	SIONS T SCAL	E PRIN	Τ.					
QTY 1ENS NO	SIONS T SCAL Ances M VISE S	E PRIN JNLESS Pecifi		DR	24MAYOO APP 24MAYOO			
QTY IEN NO ER/ ERI	SIONS T SCAL ANCES I VISE SI DEC ±	E PRIN JNLESS PECIFI .25		B.HIGM CHK 24	IAN T.ELBIN AMAYOO REL -	) AMP Incorporated Harrieburg, PA 17105-	3608	
QTY 1ENS NO ER/ ERI >LC >LC	SIONS T SCAL ANCES I VISE SI DEC ± DEC ± DEC ±	E PRIN JNLESS PECIFI .25 -		B.HIGM CHK 24	IAN T.ELBIN MAYOO REL - HIGMAN -	Harrisburg, PA 17105-		
	DEC ± DEC ± DEC ± DEC ± DEC ± DEC ± TEXTUR	E PRIN JNLESS PECIFI .25 - -	ed:	B.HIGM CHK 24 B.	ian t.elbin Mayoo rel - Higman -	MAPPLICATOR MACHINE R	ef .PPL	-
QTY IENS NO LERA ERA PLC PLC PLC FLC	DEC ± DEC ± DEC ± DEC ± DEC ±	E PRIN JNLESS PECIFI .25 - -	ed:	B.HIGM CHK 24	IAN T.ELBIN MAYOO REL - HIGMAN -	Machine Re MACHINE RE MINI A	ĒF	