

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2015

© COPYRIGHT 2015

TE Connectivity Germany GmbH

ALL RIGHTS RESERVED.

CODING C-G (GEOMETRY)
Kodierung C-G (Geometrie)

DRAWN WITHOUT LEVER
ohne Hebel gezeichnet

LEVER LOCKED
Hebel verrastet

CABLE OUTLET RIGHT
Kabelabgang rechts

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±
±
±
±
±
±
-

10
±

APVD
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
CUSTOMER DRAWING

17JAN2003
20JAN2003
21JAN2003
-

6.3 g

NAME
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1393440

RESTRICTED TO
-

SCALE
5:1

SHEET
1 OF 2

REV
B2

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A4	CHAMFER 0.6x45° REMOVED, 0.4x45° ADDED	19APR2016	MAH.	GILC
	B	SEE PCN E-19-010873	15JUL2019	SCK	MN
	B1	OBSOLETE VARIANT 2-1393440-4	09MAY2024	KMD	SCK
	B2	OBSOLETE VARIANT 1-1393440-5, 1-9, 2-2 and 2-5	16SEP2024	RG	SK

NOTES
Bemerkungen

1 COVER, COLOR SEE TABLE.
Abdeckkappe, Farbe siehe Tabelle.

2 LEVER, COLOR NATURAL
Hebel, Farbe natur

3 PART REVISION
Teile Revision

4 TE PART NO. ASSEMBLY ACCORDING TO PARTS LIST
TE-Teile Nr. Zusammenbau (ASSY) entsprechend Stueckliste

5 MATERIAL IDENTIFICATION
Materialkennzeichnung

6 CAVITY MARKING
Nestmarkierung

7 TE LOGO
TE Logo

8 COVER DIMENSION IN LEVER AREA
Abdeckkappenmass im Hebelbereich

9 PRODUCTION DATE
Produktionsdatum

10 LENGTH: DIN 16901-130; ANGLES, FORM AND POS.: DIN ISO 2768-mH
Laengen: DIN 16901-130; Winkel, Form und Lage: DIN ISO 2768-mH

11 REPLACES DRAWING NO. V23540-M1030-Y500/Y520-*7427
Ersetzt Zeichnung-Nr. V23540-M1030-Y500/Y520-*7427

12 CODING D-H AS SHOWN
Kodierung D-H wie gezeichnet

				A - F	MELON YELLOW /melonengelb	1028
Y554				A - F	MELON YELLOW /melonengelb	1028
Y551	3	3-1393440-3	B	C - F	MELON YELLOW /melonengelb	1028
Y549				D - E	MELON YELLOW /melonengelb	1028
Y547				D - F	MELON YELLOW /melonengelb	1028
Y546				B - H	MELON YELLOW /melonengelb	1028
Y544	3	3-1393440-2	B	C - H	MELON YELLOW /melonengelb	1028
Y541	3	3-1393440-1	B	C - G	MELON YELLOW /melonengelb	1028
Y515	3	1-1393440-4	B	B - E	LIGHT PINK/hellrosa	3015
Y513				C - E	HEATHER VIOLET/erikaviolett	4003
Y512	3	1-1393440-3	B	A - G	GREY WHITE/grauweiss	9002
Y510				B - G	CURRY/currygelb	1027
Y508				A - H	BEIGE/beige	1001
Y502				B - F	NATURAL/natur	--
Y500	3	1-1393440-2	B	D - H	PURE ORANGE/reinorange	2004
V23540-M1030-PART NO./ Teile Nr. SIEMENS	REV.	TE PN ASSEMBLY Zusammenbau	REV.	GEOMETRY Geometrie	COLOR Farbe 1	SIMILAR TO RAL-NO. aehnlich RAL-Nr.
CODING/Kodierung						

1471-9 (3/13)

