


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2000  
 © COPYRIGHT 2000 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
A1	-	A1 PART NUMBERS CHANGED TO TYCO	24MAR2003	ACK	G.F.



**HIGH FLEXIBILITY FLAT CABLE**

WIRE SIZE 32 AWG FLAT CONDUCTOR ( 0.65mm x 0.05mm )  
 CONDUCTOR GRID 1.27mm  
 INSULATION POLYESTER, PINK  
 TEMPERATURE RATING -40° TO +80° C  
 VOLTAGE RATING 90 V rms

REEL LENGTH 30.5m	TYCO - PN	OLD PN	DIM. A	DIM. B
	0-1437380-1	175-06G	7.6	6.35 ±0.18
	0-1437380-2	175-10G	12.7	11.43 ±0.18
	0-1437380-3	175-14G	17.8	16.51 ±0.18
	0-1437380-4	175-16G	20.3	19.05 ±0.25
	0-1437380-5	175-20G	25.4	24.13 ±0.25
	0-1437380-6	175-26G	33.0	31.75 ±0.25
	0-1437380-7	175-34G	43.2	41.91 ±0.25
	0-1437380-8	175-36G	45.7	44.45 ±0.25
	0-1437380-9	175-37G	47.0	45.73 ±0.25
	1-1437380-0	175-40G	50.8	49.53 ±0.38
	1-1437380-2	175-50G	63.5	62.23 ±0.38
	1-1437380-4	175-60G	76.2	74.93 ±0.38
	1-1437380-5	175-64G	81.3	80.01 ±0.38

FLAT CABLE FOR USE WITH ANSLEY 609 SERIES CONTACTS ONLY.  
 REQUIRES CABLE GUIDE ADAPTER FOR CORRECT TERMINATION.  
 609-WXX4 FOR SOCKET CONNECTORS ( 609-XX00M )  
 AND 609-WXX3 FOR PCB TRANSITION CONNECTORS ( 609-XXX3 ).  
 FOR ADAPTER SEE DRAWING 3-1437758-7

<small>THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION                  IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION                  SHOULD BE CONTACTED FOR THE LATEST REVISION.</small>		DWN 24MAR2003 G.ACKERMANN CHK 26MAR2003 M.SCHLEIHAUF APVD 28MAR2003 G.FELDMEIER	<b>tyco</b> Electronics tyco Electronics AMP GmbH D - 67346 Speyer
DIMENSIONS: mm 	TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.1 0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	PRODUCT SPEC - APPLICATION SPEC - WEIGHT -	NAME HIGH FLEXIBILITY FLAT CABLE ANSLEY 175 SERIES 32 AWG
MATERIAL -	FINISH -	SIZE A3	CAGE CODE 00779 DRAWING NO C-1437380-2 RESTRICTED TO -
CUSTOMER DRAWING		SCALE 20:1	SHEET 1 OF 1 REV A1