

THIS DRAWING IS UNPUBLISHED.  
DIFFUSION RESTREINTE




RELEASED FOR PUBLICATION  
LIBRE A LA DIFFUSION

20




ALL RIGHTS RESERVED.  
Tous droits reserves.

© COPYRIGHT 2011

LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION MODIFICATIONS	DATE	DWN DESS.	APVD APP.	
F	00	C	LOGO UPDATE AND CORRECTION	21APR2011	EC XR	



ECHELLE 3:1



144935-1	26 POS. MQS MODULE (MODULE MQS 26 VOIES)	BLACK (NOIR)
TE PART NUMBER (REFERENCE TE)	DESCRIPTION (DESIGNATION)	COLOR (COULEUR)

THIS DRAWING IS A CONTROLLED DOCUMENT. CE SCHEMA EST UN DOCUMENT CONTROLE.		DWN/DESSINE D. ELISEI 04MAR1993	 TE Connectivity	
DIMENSIONS: mm		CHK/VERIFIE J. LALANGE 08AVR1998		
TOLERANCES UNLESS OTHERWISE SPECIFIED: TOLERANCES NON SPECIFIEES		APVD/APPROUVE J. REVIL 08AVR1998	NAME TITRE	
±0.3		PRODUCT SPEC SPEC. PRODUIT	MODULE MQS 26 VOIES MQS 26W MODULE	
±0.1		APPLICATION SPEC SPEC. APPLICATION	SIZE FORMAT	
45°		WEIGHT MASSE APPROX.	A2	
MATERIAL MATIERE	PBT	CUSTOMER DRAWING PLAN CLIENT	CAGE CODE UNIQUEMENT POUR REFERENCE	DRAWING NO No PLAN
FINISH FINITION		SCALE ECHELLE	5:1	SHEET FEUILLE
				1 OF 1 DE 1
				REV C