










LOC		DIST		REVISONS			
A	I	P	LTR	DESCRIPTION	DATE	DWN	APVD
				C	EG00-1192-03	11JUNE2003	CS GM



CODING A
1452348-1



CODING B
1452348-2

TYCO ORDER-NUMBER	KEYING OPTIONS					
	A	B				
	1452348-1	1452348-2				
	-	1	1b	SOCKET HOUSING COD. B	PA66-GF25	BLACK
	1	-	1a	SOCKET HOUSING COD. A	PA66-GF25	BLACK
	ITEM		DESCRIPTION	MATERIAL	COLOR	

(1) IF DIMENSION IS IN PARENTS (IN) OR PARENTS (IN) DIMENSION, DIMENSIONAL TOLERANCE SHALL BE AS SPECIFIED IN THE PARENTS (IN) DIMENSION. DIMENSIONAL TOLERANCE SHALL BE AS SPECIFIED IN THE PARENTS (IN) DIMENSION.				DWN	14DEC2001		AMP Deutschland GmbH 0 - 63225 Langen
				ENR	14DEC2001		
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
mm		9 PLC ±0.15 1 PLC ±0.15 2 PLC ±0.15 3 PLC ±0.15 4 PLC ±0.15 ANGLES ±0.5°		PRODUCT SPEC	5. POS. HEATER BLOWER SWITCH CONNECTOR		
				APPLICATION SPEC	-		
MATERIAL	FINISH	WEIGHT		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
-	-	-		A1	00779	C-1452348	-
CUSTOMER DRAWING				SCALE	5:1	SHEET	1 OF 1
				REV	C		