



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

| LOC | DIST | REVISIONS | | | |
|-----|------|--------------------|---------|-----|------|
| P | LTR | DESCRIPTION | DATE | OWN | APVD |
| 0 | | REL PER NPR 00-839 | 10OCT00 | DEH | MK |



| FIBER # | COLOR |
|---------|--------|
| 1 | BLUE |
| 2 | ORANGE |
| 3 | GREEN |
| 4 | BROWN |

TRACE NUMBER{ XXXXXXXXXX
 TYCO P/N{ 1457078-1

LABEL DETAIL

1. MAX INSERTION LOSS: 1.0 dB

LIGHTRAY MPX CONNECTOR FIBER PATH

| | |
|--------------------------|-------------|
| 1.000±0.051 [39.37±2.00] | 1457078-1 |
| L | PART NUMBER |

| | | | | |
|---|--|-----------------------------|--|--------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT. | | DRN D E HODGE 10OCT00 | AMP Incorporated Harrisburg, PA 17105-3608 | |
| DIMENSIONS: METERS [INCHES] | | CHK J SHIPE 10OCT00 | AMP | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED: | | APVD M KEPKO 10OCT00 | NAME PIGTAIL, FIBER OPTIC, 4 FIBER SINGLEMODE BUFFERED FIBER, LIGHTRAY MPX(MALE) | |
| 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - FINISH | | PRODUCT SPEC | APPLICATION SPEC | RESTRICTED TO |
| MATERIAL | | WEIGHT | SIZE A2 | CAGE CODE 00779 |
| | | DRAWING NO C-1457078 | | REV 0 |
| | | CUSTOMER DRAWING | | SCALE NTS |
| | | SHEET 1 OF 1 | | |

1457078