

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2002

© COPYRIGHT 2002

Tyco Electronics AMP GmbH

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

AI

01

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C 2	ECR-11-018055	31AUG2011	GCh	GCh
	C 3	ECR-11-018919	14SEP2011	GCh	GCh

TE ORDER NO. TE Bestellnummer	SURFACE Oberflaeche	RETAINING RING MATERIAL Sicherungsring-Material	DESCRIPTION Beschreibung	PACKING UNIT Packungs- einheit
1534831-1	A2B ACC. TO DIN ISO 4042, CHROME 6 FREE A2B nach DIN ISO 4042, chrom 6 frei	ZYTEL 101LNC010	- HEXAGON NUT WITH CLAMPING DEVICE Sechskantmutter mit Klemmteil DIN EN ISO 10511-M8 (SUPERSEDED/ersetzt DIN 985) - PROPERTY CLASS: 8.8 Festigkeitsklasse: 8.8 - LOW TYPE WITH NON METALLIC INSERT (PLASTIC RING), SELF-LOCKING NUT niedrige Bauform mit nichtmetallischem Einsatz (Kunststoffring), selbstsichernd	2500
1534831-2	A3B ACC. TO DIN ISO 4042, CHROME 6 FREE A3B nach DIN ISO 4042, chrom 6 frei	ULTRAMID A4H	- RETAINING RING COLOR: BROWN Sicherungsring-Farbe: braun - TEMPERATURE RANGE: -40°C TO +160°C Temperatur Bereich: -40°C bis +160°C	1000

NOTES
Bemerkungen

1

DIMENSION DIFFER TO DIN EN ISO 10511
Bemassung abweichend von DIN EN ISO 10511

2

IN CASE OF DISCREPANCIES BETWEEN GERMAN AND
ENGLISH TEXT THE GERMAN TEXT IS BINDING
Im Falle von Unterschieden zwischen dem deutschen und
dem englischen Text ist der deutsche Text verbindlich

1

0.36

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
-

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC
1 PLC
2 PLC
3 PLC
4 PLC
ANGLES
FINISH

±
±
±
±
±
±
-

DWN
R. Schwan
CHK
U. Gassauer
APVD
R. Brand
PRODUCT SPEC
108-18849
APPLICATION SPEC
-
WEIGHT
-

20.06.02
20.06.02
-

CUSTOMER DRAWING

TE Connectivity

NAME
NUT M8 WITH PLASTIC INSERT
Mutter M8 mit Kunststoffeinlage
-

SIZE
A 3

CAGE CODE
00779

DRAWING NO
C-1534831

RESTRICTED TO
-

SCALE
1:1

SHEET
1 OF 1

REV
C 3

1470-19 (3/11)

Pro/ENGINEER DRAWING