




TIA/EIA 568B			
P1	P2		COLOR
1	3	TWISTED PAIR	WHT/ORG
2	6		ORG
3	1	TWISTED PAIR	WHT/GRN
6	2		GREEN
4	7	TWISTED PAIR	BLUE
5	8		WHT/BLU
7	4	TWISTED PAIR	WHT/BRN
8	5		BRN
SHIELD	SHIELD	*	
DRAIN	DRAIN	*	

* CONNECTOR SHIELD AND DRAIN WIRE TO BE IN CONTINUOUS CONTACT, TO PROVIDE CONTINUOUS GROUND FROM CABLE TO PLUG SHIELD.

1. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD TEC-138-702.

2. APPLICATION SPEC 114-22008.

3. WRAPPED UNCONNECTED DRAIN WIRE OVER JACKET BEFORE CONNECTING TO MOD PLUG. PROVIDE CONTINUOUS GROUND FROM CABLE SHIELD TO PLUG SHIELD.

4. ELECTRICALLY TEST FOR CONTINUITY AND SHORTS.
HI-POT: 300VDC, 50 Mohms FOR 10mS.

5. LABEL AS FOLLOWS:

DATE CODE

CUSTOMER P/N

REV

LEVEL

→ WWYY 912 ←

COUNTRY OF ORIGIN

SEE CHART

SUPPLIER CODE

IF OUTSIDE USA

OBsolete	1715.0±20.0	U	3085393Y37	1559525-3
	800.0±20.0	U	3085393Y35	1559525-2
OBsolete	510.0±20.0	U	3085393Y32	1559525-1
	L	CUSTOMER REV	CUSTOMER P/N	TYCO ELECTRONICS P/N

1	1	1	PC	LABEL, SBP100143WE5	4
2	2	2	PC	BOOT, MOD PLUG, 8P, BLUE	3
5.63	2.63	1.70	FT	CABLE, CAT5E, 26 AWG, 4 TP, GREY	2
2	2	2	PC	MOD PLUG, KIT WITH SHIELD, 8P	1
-3	-2	-1	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES, UNLESS OTHERWISE SPECIFIED:

0 PLC	±	-
1 PLC	±	-
2 PLC	±	-
3 PLC	±	-
4 PLC	±	-
ANGLES	±	-
FINISH	-	-

DWN
E.C. CLAYBAUGH
30/JUN/09

CHK
T. BEDRIN
14/JUL/09

APVD
G. GUTGOLD
14/JUL/09

PRODUCT SPEC
—

APPLICATION SPEC
—

WEIGHT
0.000000

CUSTOMER DRAWING

TE Connectivity

NAME
CABLE ASSY, MOD PLUGS ON CAT5e, 26 AWG, 4 TP [3085393Y3x]

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=1559525

RESTRICTED TO
—

SCALE
N.T.S.

SHEET
1 OF 1

REV
D