

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
CF	71	P	LTR	DESCRIPTION	DATE	DWN	APVD
			C	REVISED PER ECO-11-000540	10/JAN/11	ECC	RB

1. APPLICATION SPEC 114-5104 AND 114-5103

2. LABEL TO BE MARKED WITH:
TYCO ELECTRONICS P/N, CUSTOMER P/N, DATE CODE
AND MANUFACTURE LOCATION AS FOLLOWS:

158018-1
44553-02
MEXICO YYWW



C1 POSITION	COLOR	"L"	C2 POSITION
10	BLACK (14)	5.50	10
9	RED (2)	5.50	9
8	GREEN (13)	5.50	8
7	ORANGE (12)	5.50	3
6	BROWN (11)	5.50	6
5	WHITE (10)	5.50	5
4	VIOLET (9)	5.50	7
3	BLUE (8)	5.50	2
2	GRAY (7)	5.50	4
1	YELLOW (6)	5.50	1

-		-	158018-1
CUSTOMER REV		CUSTOMER P/N	TYCO ELECTRONICS P/N
5.50	IN	WIRE, UL 1061, 26 AWG STR, BLK	14
5.50	IN	WIRE, UL 1061, 26 AWG STR, GRN	13
5.50	IN	WIRE, UL 1061, 26 AWG STR, ORG	12
5.50	IN	WIRE, UL 1061, 26 AWG STR, BRN	11
5.50	IN	WIRE, UL 1061, 26 AWG STR, WHT	10
5.50	IN	WIRE, UL 1061, 26 AWG STR, VIO	9
5.50	IN	WIRE, UL 1061, 26 AWG STR, BLU	8
5.50	IN	WIRE, UL 1061, 26 AWG STR, GRY	7
5.50	IN	WIRE, UL 1061, 26 AWG STR, YEL	6
1	PC	CT RECEPT. CONN. 10 POS. IDC	5
1	PC	LABEL	4
1	-	3.00" GRAYLINE TUBING, GRAY	3
5.50	IN	WIRE, UL 1061, 26 AWG STR, RED	2
1	PC	CT RECEPT. CONN. 10 POS. IDC	1
-1	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± .25
3 PLC ± .062
4 PLC ± -
ANGLES ± -
FINISH

-

DWN
M KANDOLF I
CHK
C STEWART
APVD
R BRENNIAN
PRODUCT SPEC
APPLICATION SPEC
WEIGHT
CUSTOMER DRAWING

7/23/93
8/6/93
8/6/93

DESCRIPTION

CABLE ASSY, [2] CT, AMP-IN, 10P, 26AWG WIRES [44553-02]

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=158018

RESTRICTED TO
-

SCALE
NTS

SHEET
1 of 2

REV
C

Tyco Electronics


Tyco Electronics Corporation
Harrisburg, PA 17105-3608

LOC	DIST	REVISIONS					
CF	71	P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—

1. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF TYCO ELECTRONICS STANDARD TEC-138-702.
2. APPLICATION SPEC 114-5104 AND 14-5103.

3 LABEL TO BE MARKED WITH:
TYCO ELECTRONICS P/N, CUSTOMER P/N, DATE CODE
AND MANUFACTURE LOCATION AS FOLLOWS:

158018-2
44553-02
MEXICO YYWW



C1 POSITION	COLOR	"L"	C2 POSITION
10	BLACK 14	5.50	10
9	RED 2	5.50	9
8	GREEN 13	5.50	8
7	ORANGE 12	5.50	3
6	BROWN 11	5.50	6
5	WHITE 10	5.50	5
4	VIOLET 9	5.50	7
3	BLUE 8	5.50	2
2	GRAY 7	5.50	4
1	YELLOW 6	5.50	1

-		-	158018-2
CUSTOMER REV		CUSTOMER P/N	TYCO ELECTRONICS P/N
5.50	IN	WIRE, UL 1061, 26 AWG STR, BLK	14
5.50	IN	WIRE, UL 1061, 26 AWG STR, GRN	13
5.50	IN	WIRE, UL 1061, 26 AWG STR, ORG	12
5.50	IN	WIRE, UL 1061, 26 AWG STR, BRN	11
5.50	IN	WIRE, UL 1061, 26 AWG STR, WHT	10
5.50	IN	WIRE, UL 1061, 26 AWG STR, VIO	9
5.50	IN	WIRE, UL 1061, 26 AWG STR, BLU	8
5.50	IN	WIRE, UL 1061, 26 AWG STR, GRY	7
5.50	IN	WIRE, UL 1061, 26 AWG STR, YEL	6
1	PC	CT RECEPT. CONN. 10 POS. IDC	5
1	PC	LABEL	4
1	-	3.00" GRAYLINE TUBING, GRAY	3
5.50	IN	WIRE, UL 1061, 26 AWG STR, RED	2
1	PC	CT RECEPT. CONN. 10 POS. IDC	1
-2	U/M	DESCRIPTION	ITEM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL
-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± -
2 PLC ± .25
3 PLC ± .062
4 PLC ± -
ANGLES ± -
FINISH -

DWN
M KANDOLF I
7/23/93

CHK
C STEWART
8/6/93

APVD
R BRENNIAN
8/6/93

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
-

CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

NAME
CABLE ASSY, [2] CT, AMP-IN, 10P, 26AWG WIRES
[44553-02]

SIZE
A2

CAGE CODE
00779

DRAWING NO
C=158018

RESTRICTED TO
-

SCALE
NTS

SHEET
2 of 2

REV
C