

4


3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
CE	00	A	REV PER 0A00-0496-01	07DEC01	DDE MB
		B	REL PER EC 0A00-0075-03	18FEB03	LGE SM
		D	REVISE PER 0A00-0503-04	27SEP2004	BB CB
		E	REVISE PER ECR-08-015882	25AUG2008	BB DK



QTY	PART NUMBER	DESCRIPTION	ITEM NO
1	1976850-1	PROCRIMPER, AMP	2
1	1588175-1	DIESET, LC AND AMP SC/FC TYPE	1

<small>THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.</small>		DWN D. ERDMAN 29NOV2001 CHK M. BURKHOLDER 29NOV2001 APVD S. BUCHTER 29NOV2001	Tyco Electronics Tyco Electronics Harrisburg, PA 17105-3608
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±0.5 2 PLC ±0.13 3 PLC ±0.013 4 PLC ±0.0001 ANGLES ±- FINISH	PRODUCT SPEC APPLICATION SPEC	NAME DIESET, LC AND AMP SC/FC TYPE 1.6mm - 2.4mm CABLE W/ AMP PROCRIMPER
MATERIAL		WEIGHT	SIZE A2 CAGE CODE 00779 DRAWING NO 1588176 RESTRICTED TO
CUSTOMER DRAWING		SCALE 3:1	SHEET 1 OF 1 REV E