SAFETY ORGANIZATIONS

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED OR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

UL RECOGNIZED: UL 1283

CSA CERTIFIED: CSA 22.2, # 0,0.4,8 VDE APPROVEO: EN 133 200

OPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 15 AMP, 120/250 VAC.

10 AMP/40°C, 250 VAC

I THE EREDHENCY:

MAXIMUM LEAKAGE CURRENT,

EACH LINE TO GROUND:

2 μA @ 120V 50Hz 5 μA @ 250V 50Hz

OPERATING AMBIENT TEMP. RANGE: -10°C TO +40°C @ RATED CURRENT, Ic. IN AN AMBIENT, T_0 , HIGHER THAN 40°C, THE MAXIMUM OPERATING CURRENT, T_0 , IS AS FOLLOWS: $T_0 = T_0$ $T_0 = T_0$

100 - To Io=Ir -

RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: ~40°C TO +85°C HUMIDITY: 21 DAYS @ 40°C 95% RH.
CURRENT OVERLOAD TEST: 6 TIMES In FOR 8 SECONDS

CUSTOMER DRAWING CATALOG # 15SRB2 ECN # [APPRVO. DATE PJO 02MAY07

TEST SPECIFICATIONS:

INDUCTANCE: N/A mH

CAPACITANCE: (MEASURED @ 1KHz, 0.250VAC MAX., 25°C±1°C)

LINE TO GROUND: N/A LINE TO LINE: N/A DISCHARGE RESISTOR: N/A

L/G AND L/L I.R. NO DISCHARGE RESISTOR:

6000M₁ (MIN.) @ 100VDE,


20°C AND 50% RH

RECOMMENDED RECEIVING INSPECTION HIPOT:

LINE TO GROUND: 1500 VAC FOR 1 MINUTE LINE TO LINE: 1450 VOC FOR 1 MINUTE

FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE LINIT IN YOUR EQUIPMENT.



50∩-	THIRD ANGLE						
FREQUENCY HHz	1.0	5.0	10	50	100	300	PROJECTION UNLESS OTH TOLERANCE
COMMON dB	/	/	1	1	1	/	MATERIAL & This document i
OIFF. dB	/	/	/	/	/	/	and is not to b manufacturing p prior written c

PROJECTION		
UNLESS 01	HERWISE SPEC	IFIEO,
TOLERANCE	TO BE ±.025	
MATERIAL	& FINISH: AS	SUPPLIED

his document is proprietory to CORCOM INC. CAD F and is not to be reproduced nor used for nonufocturing purposes except on EDRCOM'S DRY. BY rior written consent.

TUCO Electronice ECOCCOM 620 S. BUTTERFIELD RO. HUNDELETH IL 60060

DRIG:

POWER	LINE	FILTE	R
FILE: G:\CO\15SR	9200 TYCD	5-6609987-4	
E: .75: DATE:	CATAL	DG NO.	REV
. / J . I I I I I I I I	<u>اح</u>	anna	١.

15SRB2

0