





 THE SPECIAL BULKHEAD LAYOUT IS ONLY FOR PN:1600606-2 WITH RESTRICT FLOATING.

| PART NUMBER |                                                                                     | POWER                                                                               |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                     |
|-------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|
|             |                                                                                     | P6                                                                                  | P5                                                                                  | P4                                                                                  | P3                                                                                  | P2                                                                                  | P1                                                                                  |                                                                                     |
| 1600606-6   |  |  |  |  |  |  |  |  |
| 6ACP        |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                     |                                                                                     |

[illegible]4805 (3/11)

| LOC | DIST | REVISIONS |     |             |      |     |      |
|-----|------|-----------|-----|-------------|------|-----|------|
|     |      | P         | LTR | DESCRIPTION | DATE | DWN | APVD |
| ES  | 00   | -         | -   | SEE SHEET 1 | -    | -   | -    |
|     |      |           |     |             |      |     |      |
|     |      |           |     |             |      |     |      |
|     |      |           |     |             |      |     |      |

| PART NUMBER |  | POWER |    |    |    |    |    |  |
|-------------|--|-------|----|----|----|----|----|--|
|             |  | P6    | P5 | P4 | P3 | P2 | P1 |  |
| 1600606-7   |  | RM    | RM | RM | RM | RM | RM |  |
| 6ACP        |  |       |    |    |    |    |    |  |

| PART NUMBER |  | POWER |    |    |    |    |    |  |
|-------------|--|-------|----|----|----|----|----|--|
|             |  | P6    | P5 | P4 | P3 | P2 | P1 |  |
| 1600606-8   |  | RM    | RM | RM | RM | RM | RM |  |
| 6ACP        |  |       |    |    |    |    |    |  |

| PART NUMBER |  | POWER |    |    |    |  |
|-------------|--|-------|----|----|----|--|
|             |  | P4    | P3 | P2 | P1 |  |
| 1600606-9   |  | RA    | RM | RM | RM |  |
| 4P          |  |       |    |    |    |  |


| PART NUMBER |  | POWER |    |    |    |    |    |    |  |
|-------------|--|-------|----|----|----|----|----|----|--|
|             |  | P7    | P6 | P5 | P4 | P3 | P2 | P1 |  |
| 1-1600606-0 |  | RM    |    | RM |    | RM |    | RA |  |
| 7P          |  |       |    |    |    |    |    |    |  |

| PART NUMBER |  | POWER |    |    |    |    |  |
|-------------|--|-------|----|----|----|----|--|
|             |  | P5    | P4 | P3 | P2 | P1 |  |
| 1-1600606-1 |  | RM    | RM | RM | RM | RM |  |
| 5ACP        |  |       |    |    |    |    |  |

| PART NUMBER |  | POWER |    |  |
|-------------|--|-------|----|--|
|             |  | P2    | P1 |  |
| 1-1600606-2 |  | RM    | RA |  |
| 2P          |  |       |    |  |

| PART NUMBER |  | POWER |    |    |  |
|-------------|--|-------|----|----|--|
|             |  | P3    | P2 | P1 |  |
| 1-1600606-3 |  | RA    | RM | RM |  |
| 3ACP        |  |       |    |    |  |

D9

|                                                                                       |                                        |                                   |                               |                                                                                           |               |
|---------------------------------------------------------------------------------------|----------------------------------------|-----------------------------------|-------------------------------|-------------------------------------------------------------------------------------------|---------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |                                        | DWN<br>R. GRZYBOWSKI<br>23JUL2003 |                               | <div><div>TE</div>TE Connectivity</div>                                                   |               |
| DIMENSIONS:<br>INCHES                                                                 |                                        | CHK<br>M. CORRELL<br>23JUL2003    |                               |                                                                                           |               |
|  | TOLERANCES UNLESS OTHERWISE SPECIFIED: |                                   | APVD<br>-                     | NAME<br>PANEL MOUNT CABLE RECEPTACLE<br>HOUSING, WITH GUIDES,<br>MULTI-BEAM XL, ALL POWER | RESTRICTED TO |
|                                                                                       | 0 PLC ±.01                             |                                   | PRODUCT SPEC<br>108-2157      |                                                                                           |               |
|                                                                                       | 1 PLC ±.005                            |                                   | APPLICATION SPEC<br>114-13112 |                                                                                           |               |
|                                                                                       | 2 PLC ±.0020                           |                                   | WEIGHT<br>-                   |                                                                                           |               |
| MATERIAL<br>-                                                                         | FINISH<br>-                            | ANGLES<br>±2°                     | SIZE<br>A100779C=1600606      |                                                                                           |               |
| CUSTOMER DRAWING                                                                      |                                        |                                   | SCALE<br>4:1                  | SHEET<br>3 OF 3                                                                           | REV<br>D10    |