





LOC	DIST	REVISIONS				
		FR	LTR	DESCRIPTION	DATE	DWN APVD
AF	50		1	REVISED DRAWING	23JAN10	HMR GJ

- 1 SPECIFICATION: WIRE RANGE; #18-#34 AWG.
0.16-1.02 mm [.006-.040] DIA. COPPER MAGNET WIRE.
- 2 POCKET RECOMMENDATION: 1601424
- 3 TERMINAL APPLICATION TO COMPLY WITH
TYCO ELECTRONICS SPEC 114-13166, CONSULT
TYCO ELECTRONICS PRODUCT ENGINEERING FOR PROPER
INSERTION DEPTH.
- 4 POST PLATED 2.0-3.8 MICRONS TIN OVER 2.5 MICRONS
MIN COPPER
- 5 PRELIMINARY - NOT FOR PRODUCTION.
- 6 2 TERMINALS SHOWN FOR ILLUSTRATION PURPOSES.



5	1601256-2
PART NUMBER	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN RAGHAVENDRA 23JAN10	Tyco Electronics Corporation Harriaburg, PA 17105-3608	
DIMENSIONS: mm [INCHES]		CHK G. JACONO 23JAN10	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		RPVD G. JACONO 23JAN10	PRODUCT SPEC	
		108-2085		STANDARD RANGE WIRE TO 3.60 [.142] X 0.51 [.020], OFFSET TAB SIAMEZE TERMINAL
FINISH		APPLICATION SPEC		
		3		SIZE A1
MATERIAL FULL HARD BRASS		WEIGHT —		
		CUSTOMER DRAWING		DRAWING NO C1601256
				SCALE 11:1
				REV 1