

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	11	ECN-25-329685	17JUN2025	GSK	AK

NOTES: -

1. CHARACTERS: -


- 0-9, A-Z, +, -, /, ~, ≡
- 0, 1, 6 & 9 FOLLOWED BY A FULL STOP.
- HEIGHT 1.7 - 1.9 mm
- TOLERANCE (AXIAL) ±0.75
- (ROTATIONAL) ±5°

CHEVRON CUT MARKERS: -


CHARACTERS TO BE CENTRALLY DISPOSED ON MARKER FACE AND IN THE ATTITUDE SHOWN RELATIVE TO CHEVRON.


2. MARKER LENGTHS (DIMENSION 'A'):

- WITH SINGLE MARK 3.70-4.50
- WITH DOUBLE MARK 5.75-6.25



CHEVRON CUT



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11FEB2020 GOPALAKRISHNA H V	 TE Connectivity		
		CHK 11FEB2020 ALAN KEAN			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD 11FEB2020 ALAN KEAN	NAME MARKER Z TYPE SIZE 5 STRAIGHT / CHEVRON CUT		
	0 PLC ± - 1 PLC ± 0.2 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	PRODUCT SPEC -			
MATERIAL PVC	FINISH -	APPLICATION SPEC -	SIZE A3	CAGE CODE A00YM	DRAWING NO C-1601A0001
		WEIGHT 1.35 - 1.22g/250mm	RESTRICTED TO -		
CUSTOMER DRAWING			SCALE 10:1	SHEET 1 OF 1	REV 11