

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	11	ECN-25-329685	17JUN2025	GSK	AK

NOTES: -

1. CHARACTERS: -



- 0-9, A-Z, +, -, /,~, ≡
- 0, 1, 6 & 9 FOLLOWED BY A FULL STOP.
- HEIGHT 2.6 - 2.9 mm
- TOLERANCE (AXIAL) ±0.75
- (ROTATIONAL) ±5°


CHEVRON CUT MARKERS: -

CHARACTERS TO BE CENTRALLY DISPOSED ON MARKER FACE AND IN THE ATTITUDE SHOWN RELATIVE TO CHEVRON.

2. MARKER LENGTHS (DIMENSION 'A'):

- WITH SINGLE MARK 3.70 - 4.50
- WITH DOUBLE MARK 6.50 - 7.50



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11FEB2020 GOPALAKRISHNA H V		 TE Connectivity				
		CHK 11FEB2020 ALAN KEAN						
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.2 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -		APVD 11FEB2020 ALAN KEAN	NAME MARKER Z TYPE SIZE 11 STRAIGHT / CHEVRON CUT				
			PRODUCT SPEC —					
			APPLICATION SPEC —					
			WEIGHT 3.1 – 2.8g/250mm					
			MATERIAL PVC	FINISH —	SIZE	CAGE CODE	DRAWING NO	
				A3	A00YM	C-1601A0004		—
CUSTOMER DRAWING				SCALE 10:1	SHEET 1 OF 1		REV 11	