



DRAWING MADE IN AMERICAN PROJECTION


REVISIONS				
LTR	DESCRIPTION	DATE	DWN	APVD
E1	REVISED PER ECO-09-025273	17NOV09	KK	AEG



POS. 1



OPTIONAL (2x)



SECTION A-A

ORDER NUMBER	NUMBER OF POSITIONS	2" MAX.		
		M.M.	INCH.	
161700 - 2	2	7.6	.300	
- 3	3	10.1	.398	
- 4	4	12.6	.496	
- 5	5	15.1	.594	
- 6	6	17.6	.692	
- 7	7	20.1	.791	
- 8	8	22.6	.890	
- 9	9	25.1	.988	
L - 0	10	27.6	1.087	
L - 1	11	30.1	1.185	
L - 2	12	32.6	1.283	
- 3	13	35.1	1.382	OBSOLETE
- 4	14	37.6	1.480	
- 5	15	40.1	1.579	OBSOLETE
L - 6	16	42.6	1.677	
- 7	17	45.1	1.776	
- 8	18	47.6	1.874	
- 9	19	50.1	1.973	
- 10	20	52.6	2.071	OBSOLETE

MATERIAL: HOUSING: P.B.T. 90% GLASS FIBER  
CONTACT: PH.P.A., TIN-LEAD (93/7) PLATING

△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

SEE TABLE.	SEE ABOVE.	SEE ABOVE.
ORDER NO.	MATERIAL	PLATING

**CUSTOMER COPY FOR REFERENCE ONLY**

OR DATE PVT 17-4-81

CHK DATE

DE DATE

SCALE N.T.S.

SIZE B

NO C-161700

REV E1

©1977 BY AMP-HOLLAND N.V. ALL RIGHTS RESERVED A-MP PRODUCTS COVERED BY PATENTS AND/OR PATENTS PENDING.

AMP-HOLLAND N.V. 's-Hertogenboech

NAME 2 - 30 PIN FEMALE ON MATE CONNECTOR RCPT (HEATING) FOR MINI MATCH INTERCONNECTION SYSTEM, PITCH: 2.5 MM.

Signature: *Hobley* DATE: 11/1/81

DIMENSIONS IN M.M. DO NOT SCALE PRINT DIMENSIONS MUST BE IN INCHES.