





REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	BA1	REVISED PER ECO-11-005150	29MAR2011	RK	HMR
	BB	DRAWING UPDATE DIMENSION, ADD SCHEDULE	26JUL2023	DM	AP

FOR FURTHER INFORMATION SEE DATA SHEET FOR
SERIES RGP- METAL GLAZE FIXED RESISTORS



SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN SUBHASH.M	22-DEC-08	TE Connectivity METAL GLAZE FIXED RESISTORS- TYPE RGP0207CH SERIES		
DIMENSIONS: mm		CHK PRAKASH.S	22-DEC-08			
		APVD STEPHEN.P	22-DEC-08			
		PRODUCT SPEC	-			
		APPLICATION SPEC	-	NAME		
MATERIAL		FINISH	-	SIZE	CAGE CODE	DRAWING NO
-		-	-	A3	00779	C-1623708
		WEIGHT	-	RESTRICTED TO		
		-	-	-		
CUSTOMER DRAWING			SCALE 10:1	SHEET 1 OF 2	REV BB	


REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

Schedule			
TCPN	Catalogue Number	Part Description	Part Status
1623708-1	RGP0207CHJ100M	RGP0207CH 5% 100M	Production
1623708-2	RGP0207CHJ10M	RGP0207CH 5% 10M	Production
1623708-3	RGP0207CHJ15M	RGP0207CH 5% 15M	Production
1623708-4	1623708-4	RGP0207CH 5% 1M5	Discontinued
1623708-5	RGP0207CHJ22M	RGP0207CH 5% 22M	Production
1623708-6	RGP0207CHJ33M	RGP0207CH 5% 33M	Production
1623708-7	RGP0207CHJ470M	RGP0207CH 5% 470M 5K PK	Production
1623708-8	RGP0207CHJ47M	RGP0207CH 5% 47M	Production
1623708-9	1623708-9	RGP0207CH 5% 4M7	Discontinued
1-1623708-0	RGP0207CHJ68M	RGP0207CH 5% 68M	Production
1-1623708-1	RGP0207CHJ82M	RGP0207CH 5% 82M	Production
1-1623708-2	RGP0207CHK1G0	RGP0207CH 10% 1G0	Production
1-1623708-3	1-1623708-3	RGP0207CH 5% 3M3	Discontinued
1-1623708-4	1-1623708-4	RGP0207CH 5% 2M2	Discontinued
1-1623708-5	1-1623708-5	RGP0207CH 5% 56M	Discontinued
1-1623708-6	1-1623708-6	RGP0207CH 5% 300M	Discontinued
1-1623708-7	1-1623708-7	RGP0207CH 5% 510M	Discontinued
1-1623708-8	1-1623708-8	RGP0207CH 5% 390K	Discontinued
1-1623708-9	1-1623708-9	RGP0207CH 5% 470K	Discontinued
2-1623708-0	RGP0207CHJ430M	RGP0207CH 5% 430M 5K PK	Discontinued
2-1623708-1	RGP0207CHJ27M	RGP0207CH 5% 27M	Production
2-1623708-2	RGP0207CHJ120M	RGP0207CH 5% 120M	Discontinued
2-1623708-3	RGP0207CHJ130M	RGP0207CH 5% 130M	Production
2-1623708-4	RGP0207CHJ39M	RGP0207CH 5% 39M	Discontinued
2-1623708-5	RGP0207CHJ150M	RGP0207CH 5% 150M	Production

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

-

-

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.2
1 PLC ±0.1
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±5°

FINISH

-

-

DWN SUBHASH.M 22-DEC-08

CHK PRAKASH.S 22-DEC-08

APVD STEPHEN.P 22-DEC-08

PRODUCT SPEC

-

APPLICATION SPEC

-

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME METAL GLAZE FIXED RESISTORS-
TYPE RGP0207CH SERIES

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

1623708

-

SCALE

10:1

SHEET

2

OF

2

REV

BB