

LOC
E

DIST
B

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	REVISED PER ECO-11-005150	29MAR2011	RK	HMR
	L	ECR-16-003725	12MAR2016	KR	TN

LASER MARKING: TE LOGO PN VALUE
TOLERANCE & DATE CODE

2x $\varnothing 3.3 \pm 0.2$ HOLES

21.40 ± 0.15

2.8
MIN

39.70 ± 0.15

51 MAX

72.5 MAX

3.2
MAX

8.2 ± 0.3

30 MAX

RoHS Compliant

DETAIL A
SCALE 4:1

$\varnothing 2.1 \pm 0.1$

0.5 A-B

11.0 MAX

4.0 ± 0.4

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 22.SEP.05

CHK DAVE KENNEDY

23.SEP.05

J CATCHPOLE

APVD 23.SEP.05

J CATCHPOLE

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

NAME

HSA50 WIDE BORE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-1625984

SCALE 3:1

SHEET 1 OF 1

REV L