



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B1	REVISE PER ECR-17-007538	25MAY2017	BW	RS



- 1 SINGLE PACK IN ACCORDANCE WITH SPEC 107-3275
- 2 100 TRAY PACK IN ACCORDANCE WITH SPEC 107-3275
- 3 0.76µm Au PLATING OVER 1.27µm Ni PLATING OVER 0.76µm Cu PLATING
- 4 0.08µm Au PLATING OVER 1.27µm Ni PLATING OVER 0.76µm Cu PLATING
- 5 HANDTOOL 9-1478240-0
- 6 DIE SET 9-1478248-0



RECOMMENDED
CRIMP SLEEVE
A/F HEX



RECOMMENDED
CABLE STRIPPING DIM'S



		1	1	BRASS	4	ACCESS CAP	7
		1	1	PTFE		INSULATOR	6
		1	1	BRASS	4	BODY	5
		1	1	BRASS	3	PIN	4
		1	1	PTFE		INSULATOR	3
		1	1	BERYLLIUM COPPER	4	RETAINING RING	2
		1	1	BRASS	4	CRIMP SLEEVE	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		2	1				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

MATERIAL
SEE TABLE

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH

TOLERANCES UNLESS OTHERWISE SPECIFIED:

SEE TABLE

DWN J.SANDWELL 12NOV03

CHK S.PARLOW 12NOV03

APVD F.WHEELER-KING 12NOV03

PRODUCT SPEC 108-3462

APPLICATION SPEC 411-3279

WEIGHT 0.000000

CUSTOMER DRAWING

TE Connectivity

NAME MMCX ELBOW PLUG CRIMP
RG178 50 OHMS
-

SIZE A3

CAGE CODE 00779

DRAWING NO C-1634003

RESTRICTED TO -

SCALE NTS

SHEET 1 OF 1

REV B1