



THIS DRAWING IS UNPUBLISHED.					RELEASED FOR PUBLICATION 07/NOV ,2003.					
© COPYRIGHT 2003 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.										
M63x1.5	63.0	18.0	6.7	30.0	68	64	70	34.0	44.0	1634245-8
M50x1.5	50.0	15.0	5.5	19.0	55	50	60	22.0	32.0	1634245-7
M40x1.5	40.0	15.0	4.6	16.0	43	40	46	18.0	25.0	1634245-6
M32x1.5	32.0	15.0	4.0	11.0	34	30	36	13.0	18.0	1634245-5
M25x1.5	25.0	12.0	3.5	8.0	27	24	30	10.0	14.0	1634245-4
M20x1.5	20.0	12.0	3.6	5.0	22	22	24	6.0	12.0	1634245-3
M16x1.5	16.0	12.0	3.5	3.0	18	17	19	5.0	10.0	1634245-2
M12x1.5	12.0	12.0	3.3	2.5	14	14	15	4.0	8.0	1634245-1
SIZE	TD mm	TL mm	T mm	Min. Shield Diameter mm	A/F BODY	A/F CAP	A/F NUT	Clamping Range Ø mm	TYCO Part No	



SECTION A-A

EX Metric EMC Gland M63x1.5 (silicone)	EMC Brass Gland with EMC Locknut	M63x1.5 (Thread Length 18mm)	EX approved	With Silicon Seal (IP68)	1634245-8
EX Metric EMC Gland M50x1.5 (silicone)	EMC Brass Gland with EMC Locknut	M50x1.5 (Thread Length 15mm)	EX approved	With Silicon Seal (IP68)	1634245-7
EX Metric EMC Gland M40x1.5 (silicone)	EMC Brass Gland with EMC Locknut	M40x1.5 (Thread Length 15mm)	EX approved	With Silicon Seal (IP68)	1634245-6
EX Metric EMC Gland M32x1.5 (silicone)	EMC Brass Gland with EMC Locknut	M32x1.5 (Thread Length 15mm)	EX approved	With Silicon Seal (IP68)	1634245-5
EX Metric EMC Gland M25x1.5 (silicone)	EMC Brass Gland with EMC Locknut	M25x1.5 (Thread Length 12mm)	EX approved	With Silicon Seal (IP68)	1634245-4
EX Metric EMC Gland M20x1.5 (silicone)	EMC Brass Gland with EMC Locknut	M20x1.5 (Thread Length 12mm)	EX approved	With Silicon Seal (IP68)	1634245-3
EX Metric EMC Gland M16x1.5 (silicone)	EMC Brass Gland with EMC Locknut	M16x1.5 (Thread Length 12mm)	EX approved	With Silicon Seal (IP68)	1634245-2
EX Metric EMC Gland M12x1.5 (silicone)	EMC Brass Gland with EMC Locknut	M12x1.5 (Thread Length 12mm)	EX approved	With Silicon Seal (IP68)	1634245-1
Product Description	Packaging Label Desrcption Line 1	Packaging Label Desrcption Line 2	Packaging Label Desrcption Line 3	Packaging Label Desrcption Line 4	TYCO Part No

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: MM

MATERIAL

—

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± —

2 PLC ± —

3 PLC ± —

4 PLC ± —

ANGLES ± —

FINISH —

DWN A. MOREY 07NOV03

CHK R.DYER 13NOV03

APVD F. WHEELER—KING 13NOV03

PRODUCT SPEC —

APPLICATION SPEC —

WEIGHT —

CUSTOMER DRAWING

Tyco Electronics Corporation
Bideford, UK, EX39 4HE

NAME (EX) EMC GLAND AND LOCKNUT
BRASS — NICKEL PLATE (M12 — M63)

SIZE A3

CAGE CODE 00779

DRAWING NO C=1634245

RESTRICTED TO —

SCALE NTS SHEET 1 OF 1 REV B

LOC E	DIST B	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	EBD0—0077—04	29JAN04	AM	FWK

NOTES

- 1, FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE.
- 2, ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED.

3 SILICONE RUBBER

5 NYLON PA 6, (NATURAL COLOUR).