

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	C	REVISED PER ECO-20-015267	28OCT2020	SY	HL

D

C

B





A

D

C


B

A




- 1 HOUSING MATERIAL: GLASS-FILLED POLYMER.
- 2 POST MATERIAL: COPPER ALLOY.
- 3 POST FINISH: DIN 41612 CLASS 2 IN CONTACT AREA. TIN PLATE ON POSTS.
- 4 RECOMMENDED HOLE SIZE FOR MANUAL APPLICATION OF CONNECTOR ONTO PC BOARD.
- 5 PART NUMBER, DATE CODE MARKED THIS APPROXIMATE AREA, INK OR LASER OPTIONAL.


CONTACT LAYOUT



PIN LENGTH



E= EARLY MATE. LATE BREAK / VOREILEND
S= STANDARD
L= LATE MATE, EARLY BREAK / NACHEILEND



PC BOARD LAYOUT

1-10	X	X	X	30	1645646-1
POSITIONS LOADED	C	B	A	NO. OF LOADED POSITION	ASSY PART NUMBER
	ROWS LOADED				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN KIRAN HOLAL 14DEC2013	TE Connectivity		
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:	CHK PATTERSON, ROBERT 14DEC2013			
	0 PLC ± -	APVD PATTERSON, ROBERT 14DEC2013	NAME EUROCARD TYPE C HEADER, MFBL		
	1 PLC ± -	PRODUCT SPEC	-		
	2 PLC ± -	APPLICATION SPEC	-		
	3 PLC ± -				
MATERIAL	FINISH	WEIGHT	SIZE	CAGE CODE	DRAWING NO
1 2	3	0.000000	A2	00779	C=1645646
CUSTOMER DRAWING			SCALE	SHEET	REV
			NTS	1 of 1	C