



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
H	-	P	LTR	DESCRIPTION	DATE	DWN	APVD
			G	-	-	-	-
			G1	ECR-08-014314	23-09-08	AEG	WRV
			G2	REVISED PER ECO-09-020689	24AUG09	KK	AEG



MATERIAL: HOUSING: P.B.T., 20% GLASS FILLED.
CONTACT: BRASS, TIN-LEAD (93/7) PLATING OVER NICKEL BARRIER

	ORDER NUMBER	NUMBER OF POSITIONS	"L" MAX. M.M.	"L" MAX. INCH.
OBSOLETE	164854-2	2	7.5	.296
OBSOLETE	-3	3	12.5	.493
	-4	4	17.5	.690
OBSOLETE	-5	5	22.5	.886
OBSOLETE	-6	6	27.5	1.083
1	-7	7	32.5	1.280
	-8	8	37.5	1.477
OBSOLETE	-9	9	42.5	1.674
1	-10	10	47.5	1.871
	-11	11	52.5	2.067
	-12	12	57.5	2.264
OBSOLETE	-13	13	62.5	2.461
1	-14	14	67.5	2.658
OBSOLETE	-15	15	72.5	2.855

1 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
	ANGLES ± -
MATERIAL	FINISH

SEE TABLE.	SEE ABOVE.	SEE ABOVE.		
ORDER NO.	MATERIAL	PLATING		
DWN 24APR78	Tyco Electronics Corporation 's-Hertogenbosch, Nederland	RESTRICTED TO		
CHK -				
APVD -				
PRODUCT SPEC -				
APPLICATION SPEC -	NAME	2-15 POS. FEMALE BOARD TO BOARD CONNECTOR ASS'Y FOR MINI-MATCH INTERCONNECTION SYSTEM PITCH 5.0 mm.		
WEIGHT -	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
CUSTOMER DRAWING	A3	00779	C-164854	-
SCALE	NTS	SHEET	1 OF 1	REV
				G2