



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		B2	REVISED PER ECR-15-012046	15JUN2015	I.T	W.H

D



TERMINATED VIEW

C



HOUSING


CONTACT

COVER

A SPACES AT .050 STAGGERED SPACING
=B REF

B

A




1 MOLDED PARTS: UL RATED 94V-0 THERMOPLASTIC, BLACK.

2 CONTACTS: PHOSPHOR BRONZE PER QQ-B-750.


3 CONTACTS: PLATED WITH .000030 MIN GOLD IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMINATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
OR
GOLD FLASH OVER PALLADIUM-NICKEL PLATE .000030 MIN TOTAL IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMENATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.

4 POLARIZING FEATURE DOES NOT EXIST ON SAME END AS THE POSN #1 INDICATOR ON 10 AND 14 POSN PRODUCT.


LOCALIZED GOLD
PLATING ON THIS SURFACE



DETAIL Z
SCALE 10:1
TYPICAL



1.125	2.100	2.380	2.150	43	44	1-1658622-3
1.625	3.100	3.380	3.150	63	64	1-1658622-2
1.525	2.900	3.180	2.950	59	60	1-1658622-1
1.275	2.400	2.680	2.450	49	50	1-1658622-0
1.025	1.900	2.180	1.950	39	40	1658622-9
.875	1.600	1.880	1.650	33	34	1658622-8
.775	1.400	1.680	1.450	29	30	1658622-7
.675	1.200	1.480	1.250	25	26	1658622-6
.625	1.100	1.380	1.150	23	24	1658622-5
.525	.900	1.180	.950	19	20	1658622-4
.425	.700	.980	.750	15	16	1658622-3
.375	.600	.880	.650	13	14	1658622-2
.275	.400	.680	.450	9	10	1658622-1
E	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. SAMICK 22AUG03	 TE Connectivity				
DIMENSIONS: INCHES		CHK C. RHODE 22AUG03					
	TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD M. WALMSLEY 22AUG03	NAME RECEPTACLE ASSY, CENTER & MILITARY POLARIZATION LEAD FREE AMP-LATCH™ NOVO			
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .005 4 PLC ± - ANGLES ± 5°		PRODUCT SPEC 108-40000				
	FINISH		APPLICATION SPEC 114-40005				
MATERIAL SEE NOTES	SEE NOTES		WEIGHT -	SIZE A2	CAGE CODE 00779	DRAWING NO C=1658622	RESTRICTED TO -
CUSTOMER DRAWING			SCALE 4:1		SHEET 1 of 2		REV B2

4



3

2

1

THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION
© COPYRIGHT - By -	ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
GP	00	P	LTR	DESCRIPTION	DATE	APVD
		-	-	SEE SHEET 1	-	-



1-1658622-2	9-1658622-2
SUB CONNECTOR	REEL PACKAGED PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. SAMICK	22AUG03	 TE Connectivity					
		CHK C. RHODE	22AUG03						
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M. WALMSLEY	22AUG03	NAME RECEPTACLE ASSY, CENTER & MILITARY POLARIZATION LEAD FREE AMP-LATCH NOVO	RESTRICTED TO				
	0 PLC ± -	PRODUCT SPEC 108-40000							
	1 PLC ± -	APPLICATION SPEC 114-40005	SIZE			CAGE CODE	DRAWING NO		
	2 PLC ± -								
	3 PLC ± .005								
	4 PLC ± -								
MATERIAL	FINISH	WEIGHT -		A2	00779	C-1658622			
SEE NOTES	SEE NOTES	CUSTOMER DRAWING		SCALE	4:1	SHEET	2 of 2	REV	B2

1658622