






LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
GP	00		E1	REVISED PER ECO-11-004835	11MAR11	RK
						HMR



TERMINATED VIEW



- 1
- MOLDED PARTS: UL RATED 94V-0 THERMOPLASTIC, BLACK.
- 2
- CONTACTS: PHOSPHOR BRONZE PER QQ-B-750.
- 3
- CONTACTS: PLATED WITH .000030 MIN GOLD IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMINATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
-
- OR
-
- GOLD FLASH OVER PALLADIUM-NICKEL PLATE .000030 MIN TOTAL IN LOCALIZED GOLD PLATE AREA, .000050 MIN TIN ON TERMENATION END, ALL OVER .000050 MIN NICKEL ON ENTIRE CONTACT.
- 4
- POLARIZING FEATURE DOES NOT EXIST ON SAME END AS THE POSN #1 INDICATOR ON 10 AND 14 POSN PRODUCT.



OBSOLETE	3.100	3.380	3.150	63	64	1-1658623-2
OBSOLETE	2.900	3.180	2.950	59	60	1-1658623-1
	2.400	2.680	2.450	49	50	1-1658623-0
	1.900	2.180	1.950	39	40	1658623-9
	1.600	1.880	1.650	33	34	1658623-8
	1.400	1.680	1.450	29	30	1658623-7
	1.200	1.480	1.250	25	26	1658623-6
	1.100	1.380	1.150	23	24	1658623-5
	.900	1.180	.950	19	20	1658623-4
	.700	.980	.750	15	16	1658623-3
	.600	.880	.650	13	14	1658623-2
	.400	.680	.450	9	10	1658623-1
	D	C	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
INCHES

MATERIAL

SEE NOTES

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± .005

4 PLC ± -

ANGLES ± 5°

FINISH

SEE NOTES

DWN R. SAMICK 25AUG03

CHK C. ROHDE 25AUG03

APVD M. WALMSLEY 25AUG03

PRODUCT SPEC 108-40000

APPLICATION SPEC 114-40005

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

RECEPTACLE ASSY,
MILITARY POLARIZATION,
LEAD FREE, AMP-LATCH™ NOVO

SIZE A2

CAGE CODE 00779

DRAWING NO C=1658623

RESTRICTED TO -

SCALE 4:1

SHEET 1 of 1

REV E1